



TABLE

ITEM NO	L
CAB-USB2AB/1.0-BK	1000mm±20mm
CAB-USB2AB/1.8-BK	1800mm±20mm
CAB-USB2AB/3-BK	3000mm±30mm
CAB-USB2AB/5-BK	5000mm±30mm

1.CABLE:UL2725,28AWG(7/0.12mm(CCA))x1PAIRS
+24AWG(7/0.2mm(CCA))x2C

INSULATOR:P.P FOR 28AWG&PVC 24AWG
SHIELD:AL-FOIL+DRAIN WIRE+32BRAID(ALM)
JACKET:PVC,COLOR:BLACK,D.D:4.8mm±0.2mm

2.CONNECTOR:1 PCS USB A SOLDER TYPE MALE

COLOR:WHITE COLOR
SHELL:NICKEL PLATED

3.CONNECTOR:1 PCS USB B SOLDER TYPE MALE

COLOR:WHITE COLOR
SHELL:NICKEL PLATED

4.HOOD:MOULDED BLACK COLOR

5.Fulfill ROHS Guideline

6.ELECTRONIC TEST:100% OPEN SHORT+MISS WIRE TEST

WIRE LIST

P1		P2	
USB A MALE	WIRE COLOR	USB B MALE	AWG
1	RED	1	24AWG
2	WHITE	2	1 PAIRS (28AWG)
3	GREEN	3	
4	BLACK	4	24AWG
SHELL	DRAIN	SHELL	

PART NO	CAB-USB2AB/xx-BK	SHEET NO	1	THIRD ANGLE PROJECTION		NEWMAN, HOPE & CO. INC TEL:886-2-28765517,FAX:886-2-28765527 E-MAIL: sales@newmanhope.com.tw
TITLE:USB A MALE TO USB B MALE UL2725 CABLE,BLACK COLOR						
				SIZE	A4	CHECKED BY & DATE
				UNIT		APPROVED BY & DATE
DWN NO				D-CAB-USB2AB/xx-BK	<input checked="" type="checkbox"/> mm <input type="checkbox"/> INCH	