



SIMATIC ET 200SP, Analog input module, AI 8xRTD/TC 2-wire High Feature suitable for BU type A0, A1, Color code CC00, channel diagnostics, 16 bit, +/-0.1%

General information	
Product type designation	AI 8xRTD/TC 2-wire HF
HW functional status	From FS05
Firmware version	V2.1
• FW update possible	Yes
usable BaseUnits	BU type A0, A1
Color code for module-specific color identification plate	CC00
Product function	
• I&M data	Yes; I&M0 to I&M3
• Isochronous mode	No
• Measuring range scalable	Yes
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	V16, V17 / V18
• STEP 7 configurable/integrated from version	V5.5 SP3 / V5.5 SP4
• PCS 7 configurable/integrated from version	V8.1 SP1
• PROFIBUS from GSD version/GSD revision	One GSD file each, Revision 3 and 5 and higher
• PROFINET from GSD version/GSD revision	GSDML V2.35
Operating mode	
• Oversampling	No
• MSI	No
CiR - Configuration in RUN	
Reparameterization possible in RUN	Yes
Calibration possible in RUN	Yes
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption, max.	35 mA
Power loss	
Power loss, typ.	0.75 W
Address area	
Address space per module	
• Address space per module, max.	16 byte; + 1 byte for QI information
Hardware configuration	
Automatic encoding	
• Mechanical coding element	Yes
• Type of mechanical coding element	Type A
Selection of BaseUnit for connection variants	

• 2-wire connection	BU type A0, A1
Analog inputs	
Number of analog inputs	8
permissible input voltage for voltage input (destruction limit), max.	30 V
Constant measurement current for resistance-type transmitter, typ.	2 mA
Cycle time (all channels), min.	Sum of the basic conversion times and additional processing times (depending on the parameterization of the active channels)
Technical unit for temperature measurement adjustable	Yes; °C/°F/K
Input ranges (rated values), voltages	
• -1 V to +1 V — Input resistance (-1 V to +1 V)	Yes; 16 bit incl. sign 1 MΩ
• -250 mV to +250 mV — Input resistance (-250 mV to +250 mV)	Yes; 16 bit incl. sign 1 MΩ
• -50 mV to +50 mV — Input resistance (-50 mV to +50 mV)	Yes; 16 bit incl. sign 1 MΩ
• -80 mV to +80 mV — Input resistance (-80 mV to +80 mV)	Yes; 16 bit incl. sign 1 MΩ
Input ranges (rated values), thermocouples	
• Type B — Input resistance (Type B)	Yes; 16 bit incl. sign 1 MΩ
• Type C — Input resistance (Type C)	Yes; 16 bit incl. sign 1 MΩ
• Type E — Input resistance (Type E)	Yes; 16 bit incl. sign 1 MΩ
• Type J — Input resistance (type J)	Yes; 16 bit incl. sign 1 MΩ
• Type K — Input resistance (Type K)	Yes; 16 bit incl. sign 1 MΩ
• Type L — Input resistance (Type L)	Yes; 16 bit incl. sign 1 MΩ
• Type N — Input resistance (Type N)	Yes; 16 bit incl. sign 1 MΩ
• Type R — Input resistance (Type R)	Yes; 16 bit incl. sign 1 MΩ
• Type S — Input resistance (Type S)	Yes; 16 bit incl. sign 1 MΩ
• Type T — Input resistance (Type T)	Yes; 16 bit incl. sign 1 MΩ
• Type U — Input resistance (Type U)	Yes; 16 bit incl. sign 1 MΩ
• Type TXK/TXK(L) to GOST — Input resistance (Type TXK/TXK(L) to GOST)	Yes; 16 bit incl. sign 1 MΩ
Input ranges (rated values), resistance thermometer	
• Ni 100 — Input resistance (Ni 100)	Yes; 16 bit incl. sign 1 MΩ
• Ni 1000 — Input resistance (Ni 1000)	Yes; 16 bit incl. sign 1 MΩ
• LG-Ni 1000 — Input resistance (LG-Ni 1000)	Yes; 16 bit incl. sign 1 MΩ
• Ni 120 — Input resistance (Ni 120)	Yes; 16 bit incl. sign 1 MΩ
• Ni 200 — Input resistance (Ni 200)	Yes; 16 bit incl. sign 1 MΩ
• Ni 500 — Input resistance (Ni 500)	Yes; 16 bit incl. sign 1 MΩ
• Pt 100 — Input resistance (Pt 100)	Yes; 16 bit incl. sign 1 MΩ
• Pt 1000 — Input resistance (Pt 1000)	Yes; 16 bit incl. sign 1 MΩ
• Pt 200	Yes; 16 bit incl. sign

— Input resistance (Pt 200)	1 MΩ
• Pt 500	Yes; 16 bit incl. sign
— Input resistance (Pt 500)	1 MΩ
Input ranges (rated values), resistors	
• 0 to 150 ohms	Yes; 15 bit
— Input resistance (0 to 150 ohms)	1 MΩ
• 0 to 300 ohms	Yes; 15 bit
— Input resistance (0 to 300 ohms)	1 MΩ
• 0 to 600 ohms	Yes; 15 bit
— Input resistance (0 to 600 ohms)	1 MΩ
• 0 to 3000 ohms	Yes; 15 bit
— Input resistance (0 to 3000 ohms)	1 MΩ
• 0 to 6000 ohms	Yes; 15 bit
— Input resistance (0 to 6000 ohms)	1 MΩ
• PTC	Yes; 15 bit
— Input resistance (PTC)	1 MΩ
Thermocouple (TC)	
Temperature compensation	
— parameterizable	Yes
— Reference channel of the module	Yes
— internal comparison point	Yes; with BaseUnit type A1
— Reference channel of the group	Yes
— Number of reference channel groups	4; Group 0 to 3
— fixed reference temperature	Yes
Cable length	
• shielded, max.	200 m; 50 m with thermocouples
Analog value generation for the inputs	
Measurement principle	integrating (Sigma-Delta)
Integration and conversion time/resolution per channel	
• Resolution with overrange (bit including sign), max.	16 bit
• Integration time, parameterizable	Yes
• Basic conversion time, including integration time (ms)	
— additional processing time for wire-break check	2 ms; In the ranges resistance thermometers, resistors and thermocouples
• Interference voltage suppression for interference frequency f1 in Hz	16.6 / 50 / 60 Hz
• Conversion time (per channel)	180 / 60 / 50 / (67.5 / 22.5 / 18.75) ms
Smoothing of measured values	
• Number of smoothing levels	4; None; 4/8/16 times
• parameterizable	Yes
Encoder	
Connection of signal encoders	
• for voltage measurement	Yes
• for resistance measurement with two-wire connection	Yes
• for resistance measurement with three-wire connection	No
• for resistance measurement with four-wire connection	No
Errors/accuracies	
Linearity error (relative to input range), (+/-)	0.01 %; ±0.1 % for resistance thermometers and resistance
Temperature error (relative to input range), (+/-)	0.0009 %/K; ±0.005 % / K at thermocouple
Crosstalk between the inputs, min.	-50 dB
Repeat accuracy in steady state at 25 °C (relative to input range), (+/-)	0.05 %
Operational error limit in overall temperature range	
• Voltage, relative to input range, (+/-)	0.1 %
• Resistance, relative to input range, (+/-)	0.1 %
Basic error limit (operational limit at 25 °C)	
• Voltage, relative to input range, (+/-)	0.05 %
• Resistance, relative to input range, (+/-)	0.05 %
Interference voltage suppression for $f = n \times (f1 \pm 1 \%)$, f1 = interference frequency	
• Series mode interference (peak value of interference < rated value of input range), min.	70 dB; With conversion time 67.5 / 22.5 / 18.75 ms: 40 dB
• Common mode voltage, max.	10 V

• Common mode interference, min.	90 dB
Interrupts/diagnostics/status information	
Alarms	
• Diagnostic alarm	Yes
• Limit value alarm	Yes; two upper and two lower limit values in each case
Diagnoses	
• Monitoring the supply voltage	Yes
• Wire-break	Yes; channel by channel
• Group error	Yes
• Overflow/underflow	Yes; channel by channel
Diagnostics indication LED	
• Monitoring of the supply voltage (PWR-LED)	Yes; green PWR LED
• Channel status display	Yes; green LED
• for channel diagnostics	Yes; red LED
• for module diagnostics	Yes; green/red DIAG LED
Potential separation	
Potential separation channels	
• between the channels	No
• between the channels and backplane bus	Yes
• between the channels and the power supply of the electronics	Yes
Permissible potential difference	
between the inputs (UCM)	10 V DC
Isolation	
Isolation tested with	707 V DC (type test)
Ambient conditions	
Ambient temperature during operation	
• horizontal installation, min.	-30 °C
• horizontal installation, max.	60 °C
• vertical installation, min.	-30 °C
• vertical installation, max.	50 °C
Altitude during operation relating to sea level	
• Installation altitude above sea level, max.	2 000 m; On request: Installation altitudes greater than 2 000 m
Dimensions	
Width	15 mm
Height	73 mm
Depth	58 mm
last modified:	9/7/2023 