

Cable DC Splitter 5.5 x 2.1 mm 1 x female > 4 x male

Description

This Delock splitter cable can be used for the connection of four devices which need low voltage e. g. cameras or LED-stripes to a power supply with DC connector.



Item no. 83287

EAN: 4043619832873

Country of origin: China

Package: Zip poly bag

Technical details

- Connector: 1 x DC 5.5 x 2.1 mm female
4 x DC 5.5 x 2.1 mm male
- Max. power on input: 5 A
- Max. voltage on input: 24 V
- DC pin length: ca. 10.30 mm
- Cable gauge at input (DC female): AWG 20
- Cable gauge at output (DC male): AWG 24
- Contacts: nickel plated
- Length including connector: ca. 50 cm

System requirements

- Power supply with DC 5.5 x 2.1 mm male

Package content

- Splitter cable

Interface

Connector 1:	1 x DC 5.5 x 2.1 mm female
Connector 2:	4 x DC 5.5 x 2.1 mm male

Technical characteristics

Maximum current:	5 A
Voltage:	24 V

Physical characteristics

Pin finishing:	nickel-plated
Cable gauge:	20 AWG 24 AWG
Length:	50 cm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de