

# USB Type-C™ Docking Station 4K - HDMI / USB Hub / SD - Mirco SD slot / PD 3.0 85 W Tempered Glass Surface

## Description

This docking station by Delock can be connected to a computer with a USB-C™ DP Alt Mode or Thunderbolt™ 3, Thunderbolt™ 4 or Thunderbolt™ 5 port and provides a variety of interfaces. A monitor can be operated at the **HDMI output** port by a maximum **resolution up to 4K**. **Three built-in USB Type-A and one USB-C™ port** allow the use of peripherals.

## Integrated Card Reader

In addition, the docking station with integrated card reader expands a PC or laptop by an **SD and a Micro SD slot** via the USB Type-C™ connection.

## USB Power Delivery (USB PD 3.0) support up to 85 watt

The docking station has a **USB Type-C™ Power Delivery port**. If this port is connected to the power supply of the laptop or tablet, the host device is charged with up to 85 watts during operation.

## Modern Design

The **sturdy metal frame and the surface made of tempered glass** not only provide the USB-C™ dock with durability but also give it a sophisticated look – featuring a stylishly integrated, **illuminated Delock logo**.



**Item no. 92001**

EAN: 4043619920013

Country of origin: China

Package: Retail Box

## Technical details

- Connectors:
  - 1 x USB Type-C™ male
  - 1 x HDMI female
  - 3 x USB 5 Gbps Type-A female
  - 1 x USB 2.0 USB Type-C™ female
  - 1 x SD slot
  - 1 x Micro SD slot
  - 1 x USB Type-C™ PD female (power supply)
- Resolution up to 3840 x 2160 @ 60 Hz (depending on the system and the connected hardware)
- Transmission of audio and video signals

- Supports HDCP 1.4 and 2.2
- Supports HDR
- Input power PD port: 100 W, 15 W are used for the docking station
- Output power for host: max. 85 W
- LED logo
- Metal frame
- Top side made of tempered glass
- Cable length without connectors: ca. 15 cm
- Colour: anthracite
- Dimensions (LxWxH): ca. 116 x 44 x 12 mm

---

## System requirements

- Android 14.0 or above
- Chrome OS
- Linux Kernel 6.11 or above
- Mac OS 15.3.2 or above
- Windows 10/10-64/11
- iPad Air (4th Generation) or above
- iPad Pro (3rd Generation) or above
- iPhone 15 Pro or above
- Surface Pro 9
- Device with a free USB Type-C™ port and DisplayPort alternate mode or with a free Thunderbolt™ 3, Thunderbolt™ 4 or Thunderbolt™ 5 port

---

## Package content

- USB-C™ docking station
- User manual

---

## Images



## General

Specification:	HDCP 1.4 HDCP 2.2 HDR
Supported operating system:	Chrome OS Windows 10 32-Bit Windows 10 64-Bit iPad Pro (3rd Generation) or above iPad Air (4th Generation) or above Windows 11 iPhone 15 Pro or above Android 14.0 or above Surface Pro 9 Linux Kernel 6.11 or above Mac OS 15.3.2 or above
LED indicator:	1 x

## Interface

Connectors:	1 x HDMI female 1 x SD slot 1 x USB 2.0 Type-C™ female 1 x USB Type-C™ male 3 x USB 5 Gbps Type-A female 1 x Micro SD Slot
-------------	---

## Technical characteristics

Maximum screen resolution:	3840 x 2160 @ 60 Hz
----------------------------	---------------------

## Physical characteristics

Housing material:	metal
Cable length:	15 cm
Length:	116 mm
Width:	44 mm
Height:	12 mm

Colour:	anthracite
LED colour:	blue

### Manufacturer information

---

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de