



Flexible strain relief for cables
model : F5.5x2.8/25

Dimmension

Cable cross section (A)	5.5 x 2.8 mm
Total length (F)	25mm
Working length (E)	19.4mm
Width (B)	12mm
Width (D)	9mm
Mounting hole (C)	Max 6.7 x 4.7mm
Maximum mounting wall thickness (G)	2.2mm

Other

Material

- Hydrogenated styrene butadiene block copolymer (SEBS)
- Hydrogenated styrene isoprene butadiene block copolymer (SEEPS)
- Ethylene Propylene Diene Monomer (EPDM)
- Styrene butadiene styrene block copolymer (SBS)

