



BETA 1223/S12

Set of 12 Morphos screwdrivers



Features

Designed to reduce fatigue and ensure high torque transmission even in the most demanding applications.

HIGH TORQUE TRANSMISSION

The innovative tri-material handles with a rigid polypropylene core and double soft bits ensure effective and constant force transmission. Controlled deformation zones adapt to the contact points of the palm, improving thrust and tightening efficiency.

CONTROL AND PRECISION


The ergonomic shape and designed index finger and thumb rests guarantee a firm grip and precise centring of the blade on the screw. Even with dirty hands or gloves, you achieve maximum directionality and safety during use.

PERFECT GRIP AND ANTI-ROLL

The embossed texture ensures a reliable grip even under the most difficult conditions. The triangular profile prevents rolling on the work surface and promotes stable and continuous use.

STRENGTH AND DURABILITY

The chrome-plated steel blade with sandblasted finish offers protection against corrosion and wear. The black phosphated tip ensures a precise fit with the screw and reduces the risk of slipping, prolonging the life of the tool.



TRIMATERIAL STRUCTURE

The rigid polypropylene inner core is combined with soft, high-grip bits to ensure superior torque transmission.



CONTROLLED DEFORMATION

The soft areas deform in a controlled manner, adapting to the point of contact and amplifying the thrust without fatiguing the hand.



ANTI-ROTATION

The triangular shape prevents rolling on the workbench, improving safety and stability.

1221: n. Screwdrivers for slotted head screws □ 0,4x2,5x50-0,5x3x75 0,6x3,5x100-0,8x4x125 1x5,5x125-1,2x6,5x150 1,2x8x200-1,6x10x200 mm
1222: n. Screwdrivers for cross head Phillips® screws □ PH0x3x60 - PH1x4,5x80 - PH2x6x100 - PH3x8x150 mm

Coded items

	Art.
012230022	1223/S12

Scan the QR Code to access the web tab
Specs, media and documentation in one click.

