



BETA 666/C30

Zero-Reset click-type torque wrench, in case, with sockets and extension bars



Certifications and Standards



UNI EN ISO 6789

Features

The 666/C30 kit guarantees reliability and safety in the most demanding tightening operations, offering a complete and well-organised set.

TOOLS ALWAYS IN ORDER

the metal drawer ensures protection of the internal instrumentation.

COMPLETE AND VERSATILE KIT

With its 18 pieces inside the cassette, the kit includes everything needed for professional tightening operations.



REVERSIBLE RATCHETS

72-tooth mechanism for fast and precise use of the wrench, ensuring a recovery angle of only 5°.



DOUBLE GRADUATED SCALE

High scale visibility. Easily selectable setting with extremely precise increment.



BIMATERIAL HANDLE

The ergonomic handle offers a solid and strong grip. Made of materials resistant to fuels, oils and industrial liquids

Certifications and Standards



UNI EN ISO 6789

666/30: n. ZERO-RESET click-type torque wrenches □ 60÷300 Nm
 920A: n. 1/2" square drive hexagon sockets □ 13÷32 mm
 920/20÷920/22: n. 1/2" drive extension bar 75-125-255 mm
 920/16: n. 0 adaptor, 1/2" female to 3/4" male drive E 1/2 - B 3/4

Coded items

	Art.
006661030	666/C30

Scan the QR Code to access the web tab

Specs, media and documentation in one click.

