

LED tape K-0360-24 3.6 W/m, IP20

Ref. K-0360-24

NEW



Dimensions: Width [W]: 8 mm | Height [H]: 1.2 mm | Max run length [L] : 10 m | Cut every [C]: 50 mm | LED spacing [D]: 6.25 mm



- CRI 90+
- Superior color consistency and dimming performance
- Smooth regulation of brightness

TECHNICAL SPECIFICATIONS

IP protection rating	20	Color temperature	Lumen output	Efficiency	Ref
CRI	90	 3000 K	605 lm/m	168 lm/W	K-30-0360-24
LxBy	L80B50	 3500 K	605 lm/m	168 lm/W	K-35-0360-24
Lifetime	75000 h	 4000 K	610 lm/m	169 lm/W	K-40-0360-24
Input voltage	24 V DC				
Power consumption	3.6 W/m				
MacAdam's ellipse	3 SDCM				
Number of LEDs per 1 m	160				
Number of LEDs per cut section	8 pcs				
Warranty [months]	60				

RELATED ACCESSORIES > RELATED LED > WHITE MONO

Name	IP protection rating	Power consumption	Ref.
LED tape KWP-0360-24 3.6 W/m, IP65 	65	3.6 W/m	KWP-27-0360-24 KWP-30-0360-24 KWP-35-0360-24 KWP-40-0360-24 KWP-50-0360-24
LED tape KWP-14K-0360-24 3.6 W/m, IP65 	65	3.6 W/m	KWP-14K27-0360-24 KWP-14K30-0360-24 KWP-14K35-0360-24 KWP-14K40-0360-24 KWP-14K50-0360-24

LED tape K-0360-24 3.6 W/m, IP20

Ref. K-0360-24

Name	IP protection rating	Power consumption	Ref.
LED tape KWP-8K-0360-24 3.6 W/m, IP65 NEW	65	3.6 W/m	KWP-8K27-0360-24 KWP-8K30-0360-24 KWP-8K35-0360-24 KWP-8K40-0360-24 KWP-8K50-0360-24