

# USB 10 Gbps Hub with 4 USB Type-A Ports + 1 Fast Charging Port incl. Power Supply

## Description

This solid USB hub by Delock with metal housing can be connected to a computer via the USB Type-A interface. It expands the computer by **4 USB Type-A ports**. Different USB devices such as USB flash memory, card reader, external enclosure etc. can be connected.

### Additional fast charging port

Another USB Type-A port offers the possibility to charge devices, such as smartphones with up to **2.4 A**.

### Supports USB 10 Gbps

A maximum **data transfer rate of up to 10 Gbps** can be reached.

### Inclined design

Due to the specially adapted **inclination**, the hub is ideal for the home or office desk. This makes it easy to plug in USB devices.

### Secure stand

The **rubber pads** on the bottom prevent the hub from slipping when, e.g. a USB stick or USB cable is plugged in.



**Item no. 64182**

EAN: 4043619641826

Country of origin: China

Package: Retail Box

## Technical details

- Connectors:
  - 1 x USB 10 Gbps Type-A female
  - 4 x USB 10 Gbps Type-A female
  - 1 x USB Type-A charging port (max. 5 V / 2.4 A)
  - 1 x 5 V DC jack
- Data transfer rate up to:
  - SuperSpeed USB 10 Gbps,
  - SuperSpeed USB 5 Gbps,
  - Hi-Speed 480 Mbps,
  - Full-Speed 12 Mbps,
  - Low-Speed 1.5 Mbps
- LED indicator
- Robust metal housing
- Power supply: Self-powered

- Dimensions (LxWxH): ca. 117 x 67 x 25 mm
- Colour: grey
- Plug & Play

---

## Power supply specification

- Input: AC 100 ~ 240 V / 50 ~ 60 Hz / 0.6 A
- Output: 5 V / 3 A
- Ground outside, plus inside
- Dimensions:
  - inside:  $\varnothing$  ca. 1.35 mm
  - outside:  $\varnothing$  ca. 3.5 mm
  - length: ca. 10 mm

---

## System requirements

- Chrome OS
- Linux Kernel 5.11 or above
- Mac OS 11.2.3 or above
- Windows 8.1/8.1-64/10/10-64/11
- PC or laptop with a free USB Type-A port

---

## Package content

- Hub USB 10 Gbps
- 1 x cable USB 10 Gbps Type-A male to USB 10 Gbps Type-A male, length ca. 80 cm
- External power supply
- User manual

---

## Images



## General

Function:	Plug & Play
Supported operating system:	Chrome OS Windows 10 32-Bit Windows 10 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit Windows 11 Linux Kernel 5.11 or above
LED indicator:	1 x

## Interface

Connector 1:	1 x USB 10 Gbps Type-A female
Connector 2:	4 x USB 10 Gbps Type-A female
Connector 3:	1 x DC jack
Connector 4:	1 x USB Type-A charging port (max. 5 V / 2.4 A)

## Technical characteristics

Data transfer rate:	10 Gbps
---------------------	---------

## Physical characteristics

Cable length:	80 cm
Length:	117 mm
Width:	67 mm
Height:	25.0 mm
Colour:	grey

## Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland

E-Mail	<a href="mailto:info@delock.de">info@delock.de</a>
Website	<a href="http://www.delock.de">www.delock.de</a>