

Antenna Cable N plug to SMA plug LMR/CFD100 10 m low loss

Description

The antenna cable by Delock is suitable for connecting components of radio frequency technology.



Item no. 90468

EAN: 4043619904686

Country of origin: China

Package: White Box

Technical details

- Connectors:
 - 1 x N plug >
 - 1 x SMA plug
- Impedance: 50 Ohm
- Cable type: LMR100
- Cable type: coaxial
- Cable attenuation: 0.99 dB @ 2 GHz per meter
- Cable diameter: ca. 2.79 mm
- Cable colour: black
- Smallest bending radius: 6.4 mm
- Length incl. connectors (L): ca. 10 m


System requirements

- Device with one free N or SMA port

Package content

- Antenna cable

Images



Interface

Connector 1:	1 x N male
Connector 2:	1 x SMA plug

Technical characteristics

Impedance:	50 Ohm
------------	--------

Physical characteristics

Cable category:	coaxial
Cable type:	LMR100
Cable colour:	black
Cable length incl. connectors:	10 m

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

