

7 Port USB Hub with 4 Ports 10 Gbps and 4 Fast Charging Ports with Switch and Illumination

Description

This solid USB hub by Delock with metal housing can be connected to a computer via the USB Type-A or USB-C™ interface. It expands the computer by **4 USB 5 Gbps Type-A female ports with fast charging function (5 V / 2.4 A) and 2 USB 10 Gbps Type-A female** as well as one **USB 10 Gbps USB Type-C™ port**. Connected devices such as smartphones can be charged or data can be transferred.

Extensive connectivity

Due to the specially designed adapter, the Delock hub can be quickly and easily connected to the USB Type-A socket. Thus, it can be easily connected to new devices with USB Type-C™ female and older devices that only have a USB Type-A connector. The adapter is **located directly on the cable** and therefore it cannot be lost.

LED illumination and switch

Each port can be **turned on or off** individually by using the **switches**. In addition, each USB Type-A port has a frame that lights up as soon as the port is activated.



Item no. 64326

EAN: 4043619643264

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB 10 Gbps USB Type-C™ female (host)
 - 1 x USB 10 Gbps USB Type-C™ female
 - 2 x USB 10 Gbps Type-A female
 - 4 x USB 5 Gbps Type-A charging port (max. 5 V / 2.4 A)
 - 1 x 12 V DC jack
- Data transfer rate up to 10 Gbps
- LED illumination on the USB ports
- Robust metal housing
- Power supply: Self-powered
- Electrical power:
 - USB Type-C™: max. 12 watt (5 V / 2.4 A)
 - USB 10 Gbps Type-A: max. 4.5 watt (5 V / 0.9 A)
 - USB 5 Gbps Type-A: max. 12 watt (5 V / 2.4 A)
- Dimensions (LxWxH): ca. 125 x 50 x 24 mm
- Colour: black

- Plug & Play
-

Power supply specification

- Power supply type: Euro wall power plug
 - Model identifier: SG-120400050E
 - Input voltage: 100 - 240 V
 - Input AC frequency: 50 / 60 Hz
 - Input current: 1.5 A
 - Output voltage / Output current / Output power: 12.0 V / 4.0 A / 48.0 W
 - Average active efficiency: 89.2 %
 - Efficiency at low load (10 %): 84.7 %
 - No-load power consumption: 0.09 W
 - Power supply cable length: ca. 1 m
 - DC power connector: 5.5 x 2.1 mm
 - Ground outside, plus inside
-

System requirements

- Chrome OS
 - Linux Kernel 6.2 or above
 - Mac OS 14.2.1 or above
 - Windows 10/10-64/11
 - Device with a free USB Type-C™ port or with a free Thunderbolt™ 3 or Thunderbolt™ 4 port or
 - PC or laptop with a free USB Type-A port
-

Package content

- Hub USB
- Cable USB-C™ male to USB-C™ male (with adapter to USB Type-A male), length ca. 1 m
- External power supply
- User manual

Images



General

Function:	Plug & Play
Supported operating system:	Chrome OS Windows 10 32-Bit Windows 10 64-Bit Windows 11 Linux Kernel 6.2 or above Mac OS 14.2.1 or above
LED indicator:	Power

Interface

Connector:	2 x USB 10 Gbps Type-A female 1 x USB 10 Gbps USB Type-C™ female 1 x 12 V DC jack 4 x USB 5 Gbps Type-A charging port (max. 5 V / 2.4 A)
------------	---

Technical characteristics

Data transfer rate:	10 Gbps
---------------------	---------

Physical characteristics

Length:	125 mm
Width:	50 mm
Height:	24 mm
Colour:	black

Power supply

Power supply type:	Power supply specification Euro wall power supply
Model identifier:	Power supply specification SG-120400050E
Input voltage:	Power supply specification 100 - 240 V

Input AC frequency:	Power supply specification 50 / 60 Hz
Input current:	Power supply specification 1.5 A
Output voltage / Output current / Output power:	Power supply specification 12.0 V / 4.0 A / 48.0 W
Average active efficiency:	Power supply specification 89.2 %
Efficiency at low load (10 %):	Power supply specification 84.7 %
No-load power consumption:	Power supply specification 0.09 W
Power supply connector:	Power supply specification DC male 5.5 mm x 2.1 mm Ground outside, plus inside
Cable length of power supply:	Power supply specification 1 m

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de