



Flexible strain relief for cables model : F5.5x2.8/25-WH

Dimmension	
Cable cross section (A)	5.5 x 2.8 mm
Total length (F)	25mm
Working length (E)	19.4mm
Width (B)	12mm
Width (D)	9mm
Mounting hole (C)	Max 6.7 x 4.7mm
Maximum mounting wall thickness (G)	2.2mm

Other	
Material	Hydrogenated styrene butadiene block copolymer (SEBS)
	Hydrogenated styrene isoprene butadiene block copolymer (SEEPS)
	Ethylene Propylene Diene Monomer (EPDM)
	Styrene butadiene styrene block copolymer (SBS)

