












SHEET DESCRIPTION	
CONFIGURATIONS	

		
2X2 - STANDARD (STD)	2X2 - UL V0*	
		
2X3 - STANDARD (STD)		2X3 - LENGTHENED
		
2X4 - STANDARD (STD)		
		
2X6 - STANDARD (STD)		
		
2X8 - STANDARD (STD)		
		
2X10 - STANDARD (STD)	2X10 - UL V0*	















UL V0 UNIQUE FEATURE
Partial1
SCALE 10:1

* MINOR GEOMETRY CHANGE THAN STANDARD CONFIGURATION.
SEE NOTE 2a FOR MORE INFORMATION


SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
 = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC: EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14					molex				
	mm		1.5:1											
 = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)			MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL										
 = 0	ANGULAR TOL ± 1.0 °													
 = 0	4 PLACES ±													
 = 0	3 PLACES ±			PRODUCT CUSTOMER DRAWING										
 = 0	2 PLACES ± 0.1													
 = 0	1 PLACE ± 0.2													
 = 0	0 PLACES ±			DOCUMENT NUMBER SD-33482-0001					DOC TYPE	DOC PART	REVISION			
 = 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS								THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	
 = 0					A1-SIZE	33482			GENERAL MARKET		2 OF 11			

DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16 22:02:26
-----------------	----	--------------	---------------------


18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1
SHEET DESCRIPTION KEY CONFIGURATIONS																	
2X2						2X3						2X4					
 KEY A						 KEY A						 KEY A					
 KEY B						 KEY B						 KEY B					
 KEY C						 KEY C						 KEY C					
 KEY D						 KEY D						 KEY D					

SHEET DESCRIPTION
KEY CONFIGURATIONS CONT.


2X6




KEY A



KEY B




KEY C




KEY D


2X8




KEY A



1453




100




KEY D


2X1




KEY :




KEY I



KEY :










KFYI

SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex					
mm		3:1											
GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16				MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL							
ANGULAR TOL ± 1.0°													
4 PLACES ±		INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14				DOCUMENT NUMBER SD-33482-0001		DOC TYPE PSD		DOC PART 001		REVISION E2	
3 PLACES ±													
2 PLACES ± 0.1		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				MATERIAL NUMBER		CUSTOMER GENERAL MARKET		SHEET NUMBER 4 OF 11			
1 PLACE ± 0.2													
0 PLACES ±		THIRD ANGLE PROJECTION		DRAWING A1-SIZE		SERIES 33482							
													


SHEET DESCRIPTION	
BLADE SEALED ASSEMBLY	

CHARTED DIMENSION					
DESCRIPTION	DIMENSIONS				
	A	B	C	D	E
2X2	15.54	1.75	24.40	54.45	22.23
2X3 STANDARD	19.04	3.50	26.21	54.45	22.23
2X3 LENGTHENED	19.04	3.50	26.21	56.45	22.23
2X4	22.54	1.75	27.21	54.45	22.23
2X6	29.54	1.75	32.27	54.45	22.23
2X8	36.54	1.75	38.88	54.45	22.23
2X10	43.64	1.75	45.65	54.45	22.05











PRIMARY LOCK REINFORCEMENT (PLR) SHOWN IN PRE-STAGED POSITION

SECTION W-W



PRIMARY LOCK REINFORCEMENT (PLR) SHOWN IN FINAL-LOCK POSITION

SECTION V-V

SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC:			
	DIMENSION UNITS	SCALE				
 = 0	mm	3:1				
 = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)					
 = 0	ANGULAR TOL ± 1.0°					
 = 0	4 PLACES ±					
 = 0	3 PLACES ±					
 = 0	2 PLACES ± 0.1					
 = 0	1 PLACE ± 0.2					
 = 0	0 PLACES ±					
= 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					
= 0			THIRD ANGLE PROJECTION	DRAWING	SERIES	
				A1-SIZE	33482	



EC NO: 171650					
DRWN: PMANJUNATHAC	2018/01/03				
CHK'D: MVANSLAMBROU	2018/02/16				
APPR: MVANSLAMBROU	2018/02/16				
INITIAL REVISION:					
DRWN: APROFFITT	2014/04/28				
APPR: VKOSHY	2014/05/14				

DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION
SD-33482-0001		PSD	001	E2

MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
	GENERAL MARKET	5 OF 11

SHEET DESCRIPTION	
SYSTEM PACKAGING	

CHARTED DIMENSION				
CKT	BLADE CONFIGURATION	RECEPTACLE CONFIGURATION	DIMENSIONS	
			K	L
2X2	STANDARD	W/O CLIPSLOT	72.78	28.00
		W/ CLIPSLOT	72.78	28.50
		LENGTHENED	77.21	28.00
2X3	STANDARD	W/O CLIPSLOT	72.78	28.00
		W/ CLIPSLOT		30.50
	LENGTHENED	W/O CLIPSLOT	74.79	28.00
		W/ CLIPSLOT		30.50
2X4	STANDARD	W/O CLIPSLOT	72.78	29.50
		W/ CLIPSLOT		31.50
2X6	STANDARD	W/O CLIPSLOT	72.79	35.58
		W/ CLIPSLOT		
2X8	STANDARD	W/O CLIPSLOT	72.67	42.25
		W/ CLIPSLOT		
2X10	STANDARD	STANDARD	72.78	49.05




SYMBOLS ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
	DIMENSION UNITS		SCALE		CURRENT REV DESC:					molex		
	mm		4:1									
	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16					MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL		
	ANGULAR TOL ± 1.0 °											
	4 PLACES		±		INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14					PRODUCT CUSTOMER DRAWING		
	3 PLACES		±									
	2 PLACES		± 0.1		DOCUMENT NUMBER SD-33482-0001					DOC TYPE PSD	DOC PART 001	REVISION E2
	1 PLACE		± 0.2									
	0 PLACES		±		MATERIAL NUMBER 33482					CUSTOMER GENERAL MARKET		SHEET NUMBER 6 OF 11
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS												
THIRD ANGLE PROJECTION		DRAWING		SERIES								
		A1-SIZE		33482								

SHEET DESCRIPTION
BACKSHELL NOTES


BACKSHELL NOTES: VALID UNLESS OTHERWISE SPECIFIED

1. GENERAL:


- a. APPLICATION SPECIFICATION SEE: AS-34951-001
- DESIGNED TO MATE WITH BLADE SEALED ASSEMBLY SPECIFIED IN MOLEX DRAWING SD-33482-0001.
 - SYSTEM TO BE USED WITH WIRE WITHIN DIAMETER RANGE OF 1.2mm TO 2.69mm.
 - COMPONENTS ARE OPTIONAL AND MUST BE PURCHASED SEPERATELY.
 - DESIGN IS OWNED BY SCHLEMMER FOR SCHLEMMER BACKSHELL.
 - DESIGN IS OWNED BY MOLEX FOR MOLEX BACKSHELL.
 - 90° ADAPTOR DESIGN IS OWNED BY MOLEX.
 - FOR ADDITIONAL INFORMATION SEE THE BACKSHELL COMPONENT DRAWING SD-34950-0001.




2X3




2X4




2X4



2X6



2X8



2X10

BACKSHELL CUSTOMER
MODEL NUMBER LEGEND

34950-XXXX


CUSTOMER MODEL COMPONENTS

- 0 - SCHLEMMER BACKSHELL ONLY
- 1 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY A ASSEMBLY
- 2 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY B ASSEMBLY
- 3 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY C ASSEMBLY
- 4 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY D ASSEMBLY
- 5 - MOLEX BACKSHELL ONLY
- 6 - MOLEX BACKSHELL & MX150 HOUSING KEY A ASSEMBLY
- 7 - MOLEX BACKSHELL & MX150 HOUSING KEY B ASSEMBLY
- 8 - MOLEX BACKSHELL & MX150 HOUSING KEY C ASSEMBLY
- 9 - MOLEX BACKSHELL & MX150 HOUSING KEY D ASSEMBLY

BACKSHELL FEATURES

- 1 - WITH RIBS
- 2 - WITHOUT RIBS
- 3 - 90° ADAPTOR

MX150 CIRCUIT SIZE 04, 06, 08, 12, 16, 20



90° ADAPTOR

BLADE SEALED ASSEMBLY






BACKSHELL (BKS)

SCALE 1.5:1


SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
	DIMENSION UNITS		SCALE		CURRENT REV DESC: EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14 THIRD ANGLE PROJECTION 								
	mm		1.5:1										
	GENERAL TOLERANCES (UNLESS SPECIFIED)												
	ANGULAR TOL ± 1.0 °												
	4 PLACES		±										
	3 PLACES		±										
	2 PLACES		± 0.1										
	1 PLACE		± 0.2										
	0 PLACES		±										
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS										DRAWING		SERIES
				A1-SIZE		33482				GENERAL MARKET		7 OF 11	

DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16 22:02:26
-----------------	----	--------------	---------------------

SHEET DESCRIPTION	
SCHLEMMER BACKSHELL	




SECTION A-A




SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									

DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16 22:02:26
-----------------	----	--------------	---------------------




SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
	= 0	mm	SCALE 3:1	CURRENT REV DESC: EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14								molex MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL				
																= 0
																= 0
																= 0
	= 0	GENERAL TOLERANCES (UNLESS SPECIFIED)														
	= 0	ANGULAR TOL ± 1.0 °														
	= 0	4 PLACES ±														
	= 0	3 PLACES ±														
	= 0	2 PLACES ± 0.1														
	= 0	1 PLACE ± 0.2														
	= 0	0 PLACES ±														
	= 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION 		DRAWING A1-SIZE		SERIES 33482		MATERIAL NUMBER		CUSTOMER GENERAL MARKET		SHEET NUMBER 9 OF 11		


SHEET DESCRIPTION	
SCHLEMMER BACKSHELL CONFIGURATIONS	





OVERALL MATED SYSTEM WITH BLADE AND RECEPTACLE BACKSHELL





CHARTED DIMENSIONS							
CKT	BLADE CONFIGURATION	RECEPTACLE CONFIGURATION	DIMENSIONS				
			M	N	P	R	T
2X3	STANDARD	STANDARD	106.83	32.75	31.75	29.00	29.50
	LENGTHENED		108.71				
2X4	STANDARD	STANDARD	106.83	33.50	31.90	30.70	30.70
2X6	STANDARD	STANDARD	106.83	37.84	37.27	35.83	36.83




OVERALL MATED SYSTEM WITH BLADE BACKSHELL




OVERALL MATED SYSTEM WITH RECEPTACLE BACKSHELL




BLADE SEALED ASSEMBLY WITH BLADE BACKSHELL




SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
	DIMENSION UNITS		SCALE		CURRENT REV DESC: EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14			molex MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL									
	mm		2:1														
	GENERAL TOLERANCES (UNLESS SPECIFIED)																
	ANGULAR TOL		± 1.0 °					PRODUCT CUSTOMER DRAWING									
	4 PLACES		±										DOCUMENT NUMBER SD-33482-0001		DOC TYPE PSD	DOC PART 001	REVISION E2
	3 PLACES		±														
	2 PLACES		± 0.1														
	1 PLACE		± 0.2					SHEET NUMBER 10 OF 11									
	0 PLACES		±														
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS												THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER
						A1-SIZE	33482			GENERAL MARKET							




OVERALL MATED SYSTEM WITH BLADE AND RECEPTACLE BACKSHELL




(Ø DIM AA)
MIN PASS-THRU
WITH NO CLEARANCE




OVERALL MATED SYSTEM WITH BLADE BACKSHELL




(Ø DIM AB)
MIN PASS-THRU
WITH NO CLEARANCE




OVERALL MATED SYSTEM WITH RECEPTACLE BACKSHELL




(Ø DIM AC)
MIN PASS-THRU
WITH NO CLEARANCE




BLADE SEALED ASSEMBLY WITH BLADE BACKSHELL



(Ø DIM AD)
MIN PASS-THRU
WITH NO CLEARANCE




ADD THE VALUE OF 'Y' TO THE TOTAL DIMENSION
WHENEVER ADAPTOR IS USED



(Ø DIM AE)
MIN PASS-THRU
WITH NO CLEARANCE

CHARTED DIMENSIONS


CKT	BLADE CONFIGURATION	RECEPTACLE CONFIGURATION	DIMENSIONS									
			U	V	W	X	Y	AA	AB	AC	AD	AE
2X4	STANDARD	STANDARD	115.24	94.36	93.93	75.62	32.10	32.93	32.54	32.85	31.76	56.81
2X8	STANDARD	STANDARD	132.49	102.81	102.73	84.07	36.10	45.44	45.44	42.65	45.44	68.18
2X10	STANDARD	STANDARD	132.49	102.81	102.73	84.07	36.10	45.44	45.44	42.65	45.44	68.18

SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
 = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC:					molex						
	mm		1:1													
 = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16					MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL						
 = 0																
ANGULAR TOL ± 1.0 °																
 = 0	4 PLACES ±															
 = 0	3 PLACES ±		INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14					PRODUCT CUSTOMER DRAWING								
 = 0	2 PLACES ± 0.1															
 = 0	1 PLACE ± 0.2															
 = 0	0 PLACES ±		THIRD ANGLE PROJECTION					DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION		
 = 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS							DRAWING		SERIES		SD-33482-0001		PSD		001
 = 0					A1-SIZE		33482		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER			
 = 0											GENERAL MARKET		11 OF 11			



MX150 2X2 BLADE SEALED ASSEMBLY MAT SEAL

BOM AND PIN OUT SHEET



ABBREVIATION	DESCRIPTION	COLOR	MATERIAL
A-BLK	HOUSING, KEYING OPTION A	BLACK	SPS/NYLON GF20
B-LG	HOUSING, KEYING OPTION B	LIGHT GRAY	SPS/NYLON GF20
C-BR	HOUSING, KEYING OPTION C	BROWN	SPS/NYLON GF20
D-GR	HOUSING, KEYING OPTION D	GREEN	SPS/NYLON GF20
C-DG	HOUSING, KEYING OPTION C	DARK GRAY	SPS/NYLON GF20
D-SG	HOUSING, KEYING OPTION D	STONE GRAY	SPS/NYLON GF20
A-YW	HOUSING, KEYING OPTION A	YELLOW	SPS/NYLON GF20
GCP	GROMMET CAP (PLUGGED)	BLACK	SPS/NYLON GF20
GCO	GROMMET CAP (OPEN)	BLACK	SPS/NYLON GF20
PLR	PLR	NATURAL	SPS/NYLON GF20
M	MAT SEAL	ROYAL BLUE	INHERENTLY LUBRICATED SILICONE


FOR ADDITIONAL INFORMATION SEE SD-33482-0001

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS												STATUS	COMMENTS	OPTIONAL ATTATCHMENTS SOLD SEPERATELY	
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION														BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4												
KEY A, BLACK	33482-4001	A-BLK	GCO	PLR	M												SALEABLE				
KEY B, LIGHT GRAY	33482-4002	B-LG	GCO	PLR	M												SALEABLE				
KEY C, BROWN	33482-4003	C-BR	GCO	PLR	M												NOT RECOMMENDED	SEE 33482-4103			
KEY D, GREEN	33482-4004	D-GR	GCO	PLR	M												NOT RECOMMENDED	SEE 33482-4104			
KEY A, BLACK	33482-4006	A-BLK	GCP	PLR	M		2										SALEABLE				
KEY B, LIGHT GRAY	33482-4007	B-LG	GCP	PLR	M		2										SALEABLE				
KEY C, BROWN	33482-4008	C-BR	GCP	PLR	M		2										NOT RECOMMENDED	SEE 33482-4105			
KEY D, GREEN	33482-4009	D-GR	GCP	PLR	M		2										NOT RECOMMENDED	SEE 33482-4106			
KEY A, BLACK	33482-4011	A-BLK	GCP	PLR	M		2	3									SALEABLE				
KEY B, LIGHT GRAY	33482-4012	B-LG	GCP	PLR	M		2	3									SALEABLE				
KEY C, BROWN	33482-4013	C-BR	GCP	PLR	M		2	3									NOT RECOMMENDED	SEE 33482-4107			
KEY D, GREEN	33482-4014	D-GR	GCP	PLR	M		2	3									NOT RECOMMENDED	SEE 33482-4108			
KEY A, BLACK	33482-4016	A-BLK	GCP	PLR	M	1	2	3	4								SALEABLE				
KEY B, LIGHT GRAY	33482-4017	B-LG	GCP	PLR	M	1	2	3	4								SALEABLE				
KEY C, BROWN	33482-4018	C-BR	GCP	PLR	M	1	2	3	4								NOT RECOMMENDED	SEE 33482-4109			
KEY D, GREEN	33482-4019	D-GR	GCP	PLR	M	1	2	3	4								NOT RECOMMENDED	SEE 33482-4110			
KEY A, BLACK	33482-4021	A-BLK	GCP	PLR	M	1	2	3									SALEABLE				
KEY A, BLACK	33482-4022	A-BLK	GCP	PLR	M				4								SALEABLE				
KEY A, BLACK	33482-4023	A-BLK	GCP	PLR	M			3	4								SALEABLE				
KEY A, BLACK	33482-4024	A-BLK	GCP	PLR	M			3									SALEABLE				
KEY A, BLACK	33482-4025	A-BLK	GCP	PLR	M	1	2										SALEABLE				
KEY C, DARK GRAY	33482-4103	C-DG	GCO	PLR	M												SALEABLE				
KEY D, STONE GRAY	33482-4104	D-SG	GCO	PLR	M												SALEABLE				
KEY C, DARK GRAY	33482-4105	C-DG	GCP	PLR	M		2										SALEABLE				
KEY D, STONE GRAY	33482-4106	D-SG	GCP	PLR	M		2										SALEABLE				
KEY C, DARK GRAY	33482-4107	C-DG	GCP	PLR	M		2	3									SALEABLE				
KEY D, STONE GRAY	33482-4108	D-SG	GCP	PLR	M		2	3									SALEABLE				
KEY C, DARK GRAY	33482-4109	C-DG	GCP	PLR	M	1	2	3	4								SALEABLE				
KEY D, STONE GRAY	33482-4110	D-SG	GCP	PLR	M	1	2	3	4								SALEABLE				
KEY A, BLACK	33482-4111	A-BLK	GCP	PLR	M		2		4								SALEABLE				
KEY A, YELLOW	33482-4112	A-YW	GCO	PLR	M												SALEABLE				
KEY B, LIGHT GRAY	33482-4113	B-LG	GCP	PLR	M	1											SALEABLE				
KEY A, BLACK	33482-4115	A-BLK	GCP	PLR	M	1		3									SALEABLE				
KEY C, DARK GRAY	33482-4116	C-DG	GCP	PLR	M		2		4								SALEABLE				
KEY B, LIGHT GRAY	33482-4117	B-LG	GCP	PLR	M		2		4								SALEABLE				
KEY B, LIGHT GRAY	33482-4118	B-LG	GCP	PLR	M				4								SALEABLE				
KEY A, BLACK	33482-4119	A-BLK	GCP	PLR	M	1			4								SALEABLE				



MX150 2X3 BLADE SEALED ASSEMBLY MAT SEAL

BOM AND PIN OUT SHEET



ABBREVIATION	DESCRIPTION	COLOR	MATERIAL
A-BLK	HOUSING, KEYING OPTION A	BLACK	SPS/NYLON GF20
B-LG	HOUSING, KEYING OPTION B	LIGHT GRAY	SPS/NYLON GF20
C-BR	HOUSING, KEYING OPTION C	BROWN	SPS/NYLON GF20
D-GR	HOUSING, KEYING OPTION D	GREEN	SPS/NYLON GF20
C-DG	HOUSING, KEYING OPTION C	DARK GRAY	SPS/NYLON GF20
D-SG	HOUSING, KEYING OPTION D	STONE GRAY	SPS/NYLON GF20
A-YW	HOUSING, KEYING OPTION A	YELLOW	SPS/NYLON GF20
GC	GROMMET CAP (STANDARD)	BLACK	SPS/NYLON GF20
GCL	GROMMET CAP (LENGTHENED)	BLACK	SPS/NYLON GF20
PLR	PLR	NATURAL	SPS/NYLON GF20
M	MAT SEAL	ROYAL BLUE	INHERENTLY LUBRICATED SILICONE

FOR ADDITIONAL INFORMATION SEE SD-33482-0001

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS												STATUS	COMMENTS	OPTIONAL ATTATCHMENTS SOLD SEPERATELY	
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION														BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6										
KEY A, BLACK	33482-3601	A-BLK	GC	PLR	M													SALEABLE		34950-0610	34950-0620
KEY B, LIGHT GRAY	33482-3602	B-LG	GC	PLR	M													SALEABLE		34950-0610	34950-0620
KEY C, BROWN	33482-3603	C-BR	GC	PLR	M													NOT RECOMMENDED	SEE 33482-3628	34950-0610	34950-0620
KEY D, GREEN	33482-3604	D-GR	GC	PLR	M													NOT RECOMMENDED	SEE 33482-3629	34950-0610	34950-0620
VOID KEY	33482-3605																				
KEY A, BLACK	33482-3606	A-BLK	GC	PLR	M			3										SALEABLE		34950-0610	34950-0620
KEY B, LIGHT GRAY	33482-3607	B-LG	GC	PLR	M			3										SALEABLE		34950-0610	34950-0620
KEY C, BROWN	33482-3608	C-BR	GC	PLR	M			3										NOT RECOMMENDED	SEE 33482-3638	34950-0610	34950-0620
KEY D, GREEN	33482-3609	D-GR	GC	PLR	M			3										NOT RECOMMENDED	SEE 33482-3641	34950-0610	34950-0620
VOID KEY	33482-3610																				
KEY A, BLACK	33482-3611	A-BLK	GC	PLR	M			3	4									SALEABLE		34950-0610	34950-0620
KEY B, LIGHT GRAY	33482-3612	B-LG	GC	PLR	M			3	4									SALEABLE		34950-0610	34950-0620
KEY C, BROWN	33482-3613	C-BR	GC	PLR	M			3	4									NOT RECOMMENDED	SEE 33482-3642	34950-0610	34950-0620
KEY D, GREEN	33482-3614	D-GR	GC	PLR	M			3	4									NOT RECOMMENDED	SEE 33482-3643	34950-0610	34950-0620
VOID KEY	33482-3615																				
KEY A, BLACK	33482-3616	A-BLK	GC	PLR	M			3										SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3617	A-BLK	GC	PLR	M		2											SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3618	A-BLK	GC	PLR	M					5	6							SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3619	A-BLK	GC	PLR	M		2	3	4	5								SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3620	A-BLK	GC	PLR	M	1	2	3	4	5	6							SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3621	A-BLK	GC	PLR	M	1			4	5								SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3622	A-BLK	GC	PLR	M				4	5	6							SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3623	A-BLK	GC	PLR	M					5								SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3624	A-BLK	GC	PLR	M						6							SALEABLE		34950-0610	34950-0620
KEY B, LIGHT GRAY	33482-3625	B-LG	GC	PLR	M	1				5								SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3626	A-BLK	GC	PLR	M	1	2	3	4									SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3627	A-BLK	GC	PLR	M		2	3		5	6							SALEABLE		34950-0610	34950-0620
KEY C, DARK GRAY	33482-3628	C-DG	GC	PLR	M													SALEABLE		34950-0610	34950-0620
KEY D, STONE GRAY	33482-3629	D-SG	GC	PLR	M													SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3630	A-BLK	GC	PLR	M			3			6							SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3631	A-BLK	GCL	PLR	M													SALEABLE		34950-0610	34950-0620
KEY B, LIGHT GRAY	33482-3632	B-LG	GCL	PLR	M													SALEABLE		34950-0610	34950-0620
KEY C, DARK GRAY	33482-3633	C-DG	GCL	PLR	M													SALEABLE		34950-0610	34950-0620
KEY D, STONE GRAY	33482-3634	D-SG	GCL	PLR	M													SALEABLE		34950-0610	34950-0620
KEY C, DARK GRAY	33482-3635	C-DG	GCL	PLR	M			3										SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3636	A-BLK	GCL	PLR	M			3										SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3637	A-BLK	GC	PLR	M		2				6							SALEABLE		34950-0610	34950-0620
KEY C, DARK GRAY	33482-3638	C-DG	GC	PLR	M			3										SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3639	A-BLK	GCL	PLR	M	1	2	3	4	5	6							SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3640	A-BLK	GC	PLR	M				4									SALEABLE		34950-0610	34950-0620
KEY D, STONE GRAY	33482-3641	D-SG	GC	PLR	M			3										SALEABLE		34950-0610	34950-0620
KEY C, DARK GRAY	33482-3642	C-DG	GC	PLR	M			3	4									SALEABLE		34950-0610	34950-0620
KEY D, STONE GRAY	33482-3643	D-SG	GC	PLR	M			3	4									SALEABLE		34950-0610	34950-0620
KEY A, YELLOW	33482-3644	A-YW	GC	PLR	M													SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3645	A-BLK	GC	PLR	M			3	4	5	6							SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3646	A-BLK	GC	PLR	M		2	3										SALEABLE		34950-0610	34950-0620




MX150 2X3 BLADE SEALED ASSEMBLY MAT SEAL
BOM AND PIN OUT SHEET

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS											STATUS	COMMENTS	OPTIONAL ATTATCHMENTS SOLD SEPERATELY	
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION													BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6									
KEY B, LIGHT GRAY	33482-3647	B-LG	GC	PLR	M		2	3									SALEABLE		34950-0610	34950-0620
KEY C, DARK GRAY	33482-3648	C-DG	GC	PLR	M						6						SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3649	A-BLK	GC	PLR	M				4		6						SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3650	A-BLK	GC	PLR	M	1		3		5							SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3651	A-BLK	GC	PLR	M		2		4		6						SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3652	A-BLK	GC	PLR	M	1					6						SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3653	A-BLK	GC	PLR	M		2			5							SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3654	A-BLK	GC	PLR	M	1		3	4								SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3655	A-BLK	GC	PLR	M	1	2	3		5	6						SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3656	A-BLK	GC	PLR	M	1	2	3									SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3657	A-BLK	GC	PLR	M				4	5							SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3658	A-BLK	GC	PLR	M	1											SALEABLE		34950-0610	34950-0620
KEY B, LIGHT GRAY	33482-3659	B-LG	GC	PLR	M	1											SALEABLE		34950-0610	34950-0620
KEY B, LIGHT GRAY	33482-3660	B-LG	GC	PLR	M					5							SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3661	A-BLK	GC	PLR	M	1				5							SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3662	A-BLK	GC	PLR	M			3	4		6						SALEABLE		34950-0610	34950-0620
KEY B, LIGHT GRAY	33482-3663	B-LG	GC	PLR	M					5	6						SALEABLE		34950-0610	34950-0620



MX150 2X4 BLADE SEALED ASSEMBLY MAT SEAL
BOM AND PIN OUT SHEET



ABBREVIATION	DESCRIPTION	COLOR	MATERIAL
A-BLK	HOUSING, KEYING OPTION A	BLACK	SPS/NYLON GF20
B-LG	HOUSING, KEYING OPTION B	LIGHT GRAY	SPS/NYLON GF20
C-BR	HOUSING, KEYING OPTION C	BROWN	SPS/NYLON GF20
D-GR	HOUSING, KEYING OPTION D	GREEN	SPS/NYLON GF20
C-DG	HOUSING, KEYING OPTION C	DARK GRAY	SPS/NYLON GF20
D-SG	HOUSING, KEYING OPTION D	STONE GRAY	SPS/NYLON GF20
A-YW	HOUSING, KEYING OPTION A	YELLOW	SPS/NYLON GF20
GCP	GROMMET CAP (PLUGGED)	BLACK	SPS/NYLON GF20
GCO	GROMMET CAP (OPEN)	BLACK	SPS/NYLON GF20
PLR	PLR	NATURAL	SPS/NYLON GF20
M-R	MAT SEAL	RUST RED	INHERENTLY LUBRICATED SILICONE
M-B	MAT SEAL	ROYAL BLUE	INHERENTLY LUBRICATED SILICONE

FOR ADDITIONAL INFORMATION SEE SD-33482-0001

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS												STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY					
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION														BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	90° ADAPTOR WITH RIBS	90° ADAPTOR WITHOUT RIBS		
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8												
KEY A, BLACK	33482-0801	A-BLK	GCO	PLR	M-R													PLANNED OBSOLESCENCE	SEE 33482-4801	34950-0811	34950-0821	34951-0831	34951-0841		
KEY B, LIGHT GRAY	33482-0802	B-LG	GCO	PLR	M-R													PLANNED OBSOLESCENCE	SEE 33482-4802	34950-0811	34950-0821	34951-0831	34951-0841		
KEY C, BROWN	33482-0803	C-BR	GCO	PLR	M-R													PLANNED OBSOLESCENCE	SEE 33482-4803	34950-0811	34950-0821	34951-0831	34951-0841		
KEY D, GREEN	33482-0804	D-GR	GCO	PLR	M-R													PLANNED OBSOLESCENCE	SEE 33482-4804	34950-0811	34950-0821	34951-0831	34951-0841		
VOID KEY	33482-0805																								
KEY A, BLACK	33482-0806	A-BLK	GCP	PLR	M-R				4									PLANNED OBSOLESCENCE	SEE 33482-4806	34950-0811	34950-0821	34951-0831	34951-0841		
KEY B, LIGHT GRAY	33482-0807	B-LG	GCP	PLR	M-R				4									PLANNED OBSOLESCENCE	SEE 33482-4807	34950-0811	34950-0821	34951-0831	34951-0841		
KEY C, BROWN	33482-0808	C-BR	GCP	PLR	M-R				4									PLANNED OBSOLESCENCE	SEE 33482-4808	34950-0811	34950-0821	34951-0831	34951-0841		
KEY D, GREEN	33482-0809	D-GR	GCP	PLR	M-R				4									PLANNED OBSOLESCENCE	SEE 33482-4809	34950-0811	34950-0821	34951-0831	34951-0841		
VOID KEY	33482-0810																								
KEY A, BLACK	33482-0811	A-BLK	GCP	PLR	M-R				4	5								PLANNED OBSOLESCENCE	SEE 33482-4811	34950-0811	34950-0821	34951-0831	34951-0841		
KEY B, LIGHT GRAY	33482-0812	B-LG	GCP	PLR	M-R				4	5								PLANNED OBSOLESCENCE	SEE 33482-4812	34950-0811	34950-0821	34951-0831	34951-0841		
KEY C, BROWN	33482-0813	C-BR	GCP	PLR	M-R				4	5								PLANNED OBSOLESCENCE	SEE 33482-4813	34950-0811	34950-0821	34951-0831	34951-0841		
KEY D, GREEN	33482-0814	D-GR	GCP	PLR	M-R				4	5								PLANNED OBSOLESCENCE	SEE 33482-4814	34950-0811	34950-0821	34951-0831	34951-0841		
VOID KEY	33482-0815																								
KEY A, BLACK	33482-0816	A-BLK	GCP	PLR	M-R	1			4	5								PLANNED OBSOLESCENCE	SEE 33482-4816	34950-0811	34950-0821	34951-0831	34951-0841		
KEY B, LIGHT GRAY	33482-0817	B-LG	GCP	PLR	M-R	1			4	5								PLANNED OBSOLESCENCE	SEE 33482-4817	34950-0811	34950-0821	34951-0831	34951-0841		
KEY C, BROWN	33482-0818	C-BR	GCP	PLR	M-R	1			4	5								PLANNED OBSOLESCENCE	SEE 33482-4818	34950-0811	34950-0821	34951-0831	34951-0841		
KEY D, GREEN	33482-0819	D-GR	GCP	PLR	M-R	1			4	5								PLANNED OBSOLESCENCE	SEE 33482-4819	34950-0811	34950-0821	34951-0831	34951-0841		
VOID KEY	33482-0820																								
KEY A, BLACK	33482-0821	A-BLK	GCP	PLR	M-R	1			4	5			8					PLANNED OBSOLESCENCE	SEE 33482-4821	34950-0811	34950-0821	34951-0831	34951-0841		
KEY B, LIGHT GRAY	33482-0822	B-LG	GCP	PLR	M-R	1			4	5			8					PLANNED OBSOLESCENCE	SEE 33482-4822	34950-0811	34950-0821	34951-0831	34951-0841		
KEY C, BROWN	33482-0823	C-BR	GCP	PLR	M-R	1			4	5			8					PLANNED OBSOLESCENCE	SEE 33482-4823	34950-0811	34950-0821	34951-0831	34951-0841		
KEY D, GREEN	33482-0824	D-GR	GCP	PLR	M-R	1			4	5			8					PLANNED OBSOLESCENCE	SEE 33482-4824	34950-0811	34950-0821	34951-0831	34951-0841		
VOID KEY	33482-0825																								
KEY A, BLACK	33482-0826	A-BLK	GCP	PLR	M-R	1	2	3			6	7	8					PLANNED OBSOLESCENCE	SEE 33482-4826	34950-0811	34950-0821	34951-0831	34951-0841		
KEY A, BLACK	33482-0827	A-BLK	GCP	PLR	M-R								8					PLANNED OBSOLESCENCE	SEE 33482-4827	34950-0811	34950-0821	34951-0831	34951-0841		
KEY A, BLACK	33482-0828	A-BLK	GCP	PLR	M-R			3		5								PLANNED OBSOLESCENCE	SEE 33482-4828	34950-0811	34950-0821	34951-0831	34951-0841		
KEY A, BLACK	33482-0829	A-BLK	GCP	PLR	M-R		2	3	4	5	6	7						PLANNED OBSOLESCENCE	SEE 33482-4829	34950-0811	34950-0821	34951-0831	34951-0841		
KEY A, BLACK	33482-0830	A-BLK	GCP	PLR	M-R						6							PLANNED OBSOLESCENCE	SEE 33482-4830	34950-0811	34950-0821	34951-0831	34951-0841		
KEY A, BLACK	33482-0831	A-BLK	GCP	PLR	M-R			3		5	6							PLANNED OBSOLESCENCE	SEE 33482-4831	34950-0811	34950-0821	34951-0831	34951-0841		
KEY A, BLACK	33482-0832	A-BLK	GCP	PLR	M-R					5	6		8					PLANNED OBSOLESCENCE	SEE 33482-4832	34950-0811	34950-0821	34951-0831	34951-0841		
KEY A, BLACK	33482-0833	A-BLK	GCP	PLR	M-R	1		3		5								PLANNED OBSOLESCENCE	SEE 33482-4833	34950-0811	34950-0821	34951-0831	34951-0841		
KEY A, BLACK	33482-0834	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6	7	8					PLANNED OBSOLESCENCE	SEE 33482-4834	34950-0811	34950-0821	34951-0831	34951-0841		
KEY A, BLACK	33482-0835	A-BLK	GCP	PLR	M-R							7	8					PLANNED OBSOLESCENCE	SEE 33482-4835	34950-0811	34950-0821	34951-0831	34951-0841		
KEY A, BLACK	33482-0836	A-BLK	GCP	PLR	M-R		2	3			6	7	8					PLANNED OBSOLESCENCE	SEE 33482-4836	34950-0811	34950-0821	34951-0831	34951-0841		
KEY A, BLACK	33482-0837	A-BLK	GCP	PLR	M-R	1			4									PLANNED OBSOLESCENCE	SEE 33482-4837	34950-0811	34950-0821	34951-0831	34951-0841		
KEY A, BLACK	33482-0838	A-BLK	GCP	PLR	M-R		2	3		5	6	7	8					PLANNED OBSOLESCENCE	SEE 33482-4838	34950-0811	34950-0821	34951-0831	34951-0841		
KEY B, LIGHT GRAY	33482-0839	B-LG	GCP	PLR	M-R								8					PLANNED OBSOLESCENCE	SEE 33482-4839	34950-0811	34950-0821	34951-0831	34951-0841		
KEY A, BLACK	33482-0840	A-BLK	GCP	PLR	M-R		2	3		5	6		8					PLANNED OBSOLESCENCE	SEE 33482-4840	34950-0811	34950-0821	34951-0831	34951-0841		
KEY A, BLACK	33482-0841	A-BLK	GCP	PLR	M-R						6	7						PLANNED OBSOLESCENCE	SEE 33482-4841	34950-0811	34950-0821	34951-0831	34951-0841		
KEY A, BLACK	33482-0842	A-BLK	GCP	PLR	M-R							7						PLANNED OBSOLESCENCE	SEE 33482-4842	34950-0811	34950-0821	34951-0831	34951-0841		
KEY A, BLACK	33482-0843	A-BLK	GCP	PLR	M-R				4			7						PLANNED OBSOLESCENCE	SEE 33482-4843	34950-0811	34950-0821	34951-0831	34951-0841		
KEY A, BLACK	33482-0844	A-BLK	GCP	PLR	M-R			3			6							PLANNED OBSOLESCENCE	SEE 33482-4844	34950-0811	34950-0821	34951-0831	34951-0841		
KEY A, BLACK	33482-0845	A-BLK	GCP	PLR	M-R		2	3	4	5	6							PLANNED OBSOLESCENCE	SEE 33482-4845	34950-0811	34950-0821	34951-0831	34951-0841		
KEY A, BLACK	33482-0846	A-BLK	GCP	PLR	M-R				4	5		7	8					PLANNED OBSOLESCENCE	SEE 33482-4846	34950-0811	34950-0821	34951-0831	34951-0841		
KEY B, LIGHT GRAY	33482-0847	B-LG	GCP	PLR	M-R	1	2	3	4	5	6	7	8					PLANNED OBSOLESCENCE	SEE 33482-4847	34950-0811	34950-0821	34951-0831	34951-0841		
KEY A, BLACK	33482-0848	A-BLK	GCP	PLR	M-R	1				5								PLANNED OBSOLESCENCE	SEE 33482-4848	34950-0811	34950-0821	34951-0831	34951-0841		
KEY B, LIGHT GRAY	33482-0849	B-LG	GCP	PLR	M-R	1					6							PLANNED OBSOLESCENCE	SEE 33482-4849	34950-0811	34950-0821	34951-0831	34951-0841		
KEY A, YELLOW	33482-0850	A-YW	GCP	PLR	M-R	1			4									PLANNED OBSOLESCENCE	SEE 33482-4850	34950-0811	34950-0821	34951-0831	34951-0841		
KEY A, YELLOW	33482-0851	A-YW	GCO	PLR	M-R													PLANNED OBSOLESCENCE	SEE 33482-4851	34950-0811	34950-0821	34951-0831	34951-0841		
KEY C, DARK GRAY	33482-0852	C-DG	GCO	PLR	M-R													PLANNED OBSOLESCENCE	SEE 33482-4852	34950-0811	34950-0821	34951-0831	34951-0841		
KEY D, STONE GRAY	33482-0853	D-SG	GCO	PLR	M-R													PLANNED OBSOLESCENCE	SEE 33482-4853	34950-0811	34950-0821	34951-0831	34951-0841		

MX150 2X6 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

Diagram illustrating the components of the MX150 2X6 Blade Sealed Assembly:

- GROMMET CAP
- CONNECTOR HOUSING
- PRIMARY LOCK REINFORCEMENT (PLR)
- MAT SEAL

Terminal positions are labeled on the main assembly:

- TERMINAL POSITION 1
- TERMINAL POSITION 6
- TERMINAL POSITION 7
- TERMINAL POSITION 12

ABBREVIATION	DESCRIPTION	COLOR	MATERIAL
A-BLK	HOUSING, KEYING OPTION A	BLACK	SPS/NYLON GF20
B-LG	HOUSING, KEYING OPTION B	LIGHT GRAY	SPS/NYLON GF20
C-BR	HOUSING, KEYING OPTION C	BROWN	SPS/NYLON GF20
D-GR	HOUSING, KEYING OPTION D	GREEN	SPS/NYLON GF20
A-YL	HOUSING, KEYING OPTION A	YELLOW	SPS/NYLON GF20
C-DG	HOUSING, KEYING OPTION C	DARK GRAY	SPS/NYLON GF20
D-SG	HOUSING, KEYING OPTION D	STONE GRAY	SPS/NYLON GF20
GCP	GROMMET CAP (PLUGGED)	BLACK	SPS/NYLON GF20
PLR	PLR	NATURAL	SPS/NYLON GF20
M-R	MAT SEAL	RUST RED	INHERENTLY LUBRICATED SILICONE
M-B	MAT SEAL	ROYAL BLUE	INHERENTLY LUBRICATED SILICONE

FOR ADDITIONAL INFORMATION SEE SD-33482-0001

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS												STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY	
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION														BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12				
KEY A, BLACK	33482-1201	A-BLK	GCP	PLR	M-R													PLANNED OBSOLESCENCE	SEE 33482-6201	34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1202	B-LG	GCP	PLR	M-R													PLANNED OBSOLESCENCE	SEE 33482-6202	34950-1210	34950-1220
KEY C, BROWN	33482-1203	C-BR	GCP	PLR	M-R													PLANNED OBSOLESCENCE	SEE 33482-6203	34950-1210	34950-1220
KEY D, GREEN	33482-1204	D-GR	GCP	PLR	M-R													PLANNED OBSOLESCENCE	SEE 33482-6204	34950-1210	34950-1220
VOID KEY	33482-1205																				
KEY A, BLACK	33482-1206	A-BLK	GCP	PLR	M-R						6							PLANNED OBSOLESCENCE	SEE 33482-6206	34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1207	B-LG	GCP	PLR	M-R						6							PLANNED OBSOLESCENCE	SEE 33482-6207	34950-1210	34950-1220
KEY C, BROWN	33482-1208	C-BR	GCP	PLR	M-R						6							PLANNED OBSOLESCENCE	SEE 33482-6208	34950-1210	34950-1220
KEY D, GREEN	33482-1209	D-GR	GCP	PLR	M-R						6							PLANNED OBSOLESCENCE	SEE 33482-6209	34950-1210	34950-1220
VOID KEY	33482-1210																				
KEY A, BLACK	33482-1211	A-BLK	GCP	PLR	M-R						6	7						PLANNED OBSOLESCENCE	SEE 33482-6211	34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1212	B-LG	GCP	PLR	M-R						6	7						PLANNED OBSOLESCENCE	SEE 33482-6212	34950-1210	34950-1220
KEY C, BROWN	33482-1213	C-BR	GCP	PLR	M-R						6	7						PLANNED OBSOLESCENCE	SEE 33482-6213	34950-1210	34950-1220
KEY D, GREEN	33482-1214	D-GR	GCP	PLR	M-R						6	7						PLANNED OBSOLESCENCE	SEE 33482-6214	34950-1210	34950-1220
VOID KEY	33482-1215																				
KEY A, BLACK	33482-1216	A-BLK	GCP	PLR	M-R	1					6	7						PLANNED OBSOLESCENCE	SEE 33482-6216	34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1217	B-LG	GCP	PLR	M-R	1					6	7						PLANNED OBSOLESCENCE	SEE 33482-6217	34950-1210	34950-1220
KEY C, BROWN	33482-1218	C-BR	GCP	PLR	M-R	1					6	7						PLANNED OBSOLESCENCE	SEE 33482-6218	34950-1210	34950-1220
KEY D, GREEN	33482-1219	D-GR	GCP	PLR	M-R	1					6	7						PLANNED OBSOLESCENCE	SEE 33482-6219	34950-1210	34950-1220
VOID KEY	33482-1220																				
KEY A, BLACK	33482-1221	A-BLK	GCP	PLR	M-R	1					6	7					12	PLANNED OBSOLESCENCE	SEE 33482-6221	34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1222	B-LG	GCP	PLR	M-R	1					6	7					12	PLANNED OBSOLESCENCE	SEE 33482-6222	34950-1210	34950-1220
KEY C, BROWN	33482-1223	C-BR	GCP	PLR	M-R	1					6	7					12	PLANNED OBSOLESCENCE	SEE 33482-6223	34950-1210	34950-1220
KEY D, GREEN	33482-1224	D-GR	GCP	PLR	M-R	1					6	7					12	PLANNED OBSOLESCENCE	SEE 33482-6224	34950-1210	34950-1220
VOID KEY	33482-1225																				
KEY A, BLACK	33482-1226	A-BLK	GCP	PLR	M-R						6						12	PLANNED OBSOLESCENCE	SEE 33482-6226	34950-1210	34950-1220
KEY A, BLACK	33482-1227	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6	7	8	9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6227	34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1228	B-LG	GCP	PLR	M-R	1	2	3	4	5	6	7	8	9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6228	34950-1210	34950-1220
KEY C, BROWN	33482-1229	C-BR	GCP	PLR	M-R	1	2	3	4	5	6	7	8	9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6229	34950-1210	34950-1220
KEY D, GREEN	33482-1230	D-GR	GCP	PLR	M-R	1	2	3	4	5	6	7	8	9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6230	34950-1210	34950-1220
VOID KEY	33482-1231																				
KEY A, BLACK	33482-1232	A-BLK	GCP	PLR	M-R		2	3					8			11		PLANNED OBSOLESCENCE	SEE 33482-6232	34950-1210	34950-1220
KEY A, BLACK	33482-1233	A-BLK	GCP	PLR	M-R		2	3		5	6	7	8			11		PLANNED OBSOLESCENCE	SEE 33482-6233	34950-1210	34950-1220
KEY A, BLACK	33482-1234	A-BLK	GCP	PLR	M-R						6	7						PLANNED OBSOLESCENCE	SEE 33482-6234	34950-1210	34950-1220
KEY A, BLACK	33482-1235	A-BLK	GCP	PLR	M-R		2	3			6	7	8		10	11		PLANNED OBSOLESCENCE	SEE 33482-6235	34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1236	B-LG	GCP	PLR	M-R	1				5	6	7	8	9	10			PLANNED OBSOLESCENCE	SEE 33482-6236	34950-1210	34950-1220
KEY A, BLACK	33482-1237	A-BLK	GCP	PLR	M-R		2											PLANNED OBSOLESCENCE	SEE 33482-6237	34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1238	B-LG	GCP	PLR	M-R		2							9	10			PLANNED OBSOLESCENCE	SEE 33482-6238	34950-1210	34950-1220
KEY A, BLACK	33482-1239	A-BLK	GCP	PLR	M-R	1				5	6	7	8					PLANNED OBSOLESCENCE	SEE 33482-6239	34950-1210	34950-1220
KEY A, BLACK	33482-1240	A-BLK	GCP	PLR	M-R		2	3					8	9	10	11		PLANNED OBSOLESCENCE	SEE 33482-6240	34950-1210	34950-1220
KEY A, BLACK	33482-1241	A-BLK	GCP	PLR	M-R							7	8	9	10	11		PLANNED OBSOLESCENCE	SEE 33482-6241	34950-1210	34950-1220
KEY A, BLACK	33482-1242	A-BLK	GCP	PLR	M-R							7	8					PLANNED OBSOLESCENCE	SEE 33482-6242	34950-1210	34950-1220
KEY A, BLACK	33482-1243	A-BLK	GCP	PLR	M-R		2							9	10			PLANNED OBSOLESCENCE	SEE 33482-6243	34950-1210	34950-1220
KEY A, BLACK	33482-1244	A-BLK	GCP	PLR	M-R		2		4									PLANNED OBSOLESCENCE	SEE 33482-6244	34950-1210	34950-1220
KEY A, BLACK	33482-1245	A-BLK	GCP	PLR	M-R									9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6245	34950-1210	34950-1220
KEY A, BLACK	33482-1246	A-BLK	GCP	PLR	M-R											11		PLANNED OBSOLESCENCE	SEE 33482-6246	34950-1210	34950-1220
KEY A, BLACK	33482-1247	A-BLK	GCP	PLR	M-R		2	3	4			7	8					PLANNED OBSOLESCENCE	SEE 33482-6247	34950-1210	34950-1220
KEY A, BLACK	33482-1248	A-BLK	GCP	PLR	M-R	1		3	4	5	6	7	8					PLANNED OBSOLESCENCE	SEE 33482-6248	34950-1210	34950-1220
KEY A, BLACK	33482-1249	A-BLK	GCP	PLR	M-R										10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6249	34950-1210	34950-1220



MX150 2X6 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS												STATUS	COMMENTS	OPTIONAL ATTATCHMENTS SOLD SEPERATELY			
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION														BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS		
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12						
KEY A, BLACK	33482-6239	A-BLK	GCP	PLR	M-B	1				5	6	7	8					SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6240	A-BLK	GCP	PLR	M-B		2	3					8	9	10	11		SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6241	A-BLK	GCP	PLR	M-B							7	8	9	10	11		SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6242	A-BLK	GCP	PLR	M-B							7	8					SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6243	A-BLK	GCP	PLR	M-B			2						9	10			SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6244	A-BLK	GCP	PLR	M-B		2		4									SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6245	A-BLK	GCP	PLR	M-B									9	10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6246	A-BLK	GCP	PLR	M-B											11		SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6247	A-BLK	GCP	PLR	M-B		2	3	4			7	8					SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6248	A-BLK	GCP	PLR	M-B	1		3	4	5	6	7	8					SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6249	A-BLK	GCP	PLR	M-B										10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6250	A-BLK	GCP	PLR	M-B				4	5	6	7	8	9				SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6251	A-BLK	GCP	PLR	M-B		2		4	5			8		10	11		SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6252	A-BLK	GCP	PLR	M-B							7						SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6253	A-BLK	GCP	PLR	M-B		2	3	4	5	6	7	8		10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6254	A-BLK	GCP	PLR	M-B		2	3	4	5					10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6255	A-BLK	GCP	PLR	M-B		2	3	4	5	6	7			10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6256	A-BLK	GCP	PLR	M-B	1					6	7		9				SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6257	A-BLK	GCP	PLR	M-B									9	10		12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6258	A-BLK	GCP	PLR	M-B		2	3								11		SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6259	A-BLK	GCP	PLR	M-B	1	2	3	4	5				9	10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6260	A-BLK	GCP	PLR	M-B											11	12	SALEABLE		34950-1210	34950-1220		
KEY C, DARK GRAY	33482-6261	C-DG	GCP	PLR	M-B													SALEABLE		34950-1210	34950-1220		
KEY D, STONE GRAY	33482-6262	D-SG	GCP	PLR	M-B													SALEABLE		34950-1210	34950-1220		
KEY C, DARK GRAY	33482-6263	C-DG	GCP	PLR	M-B	1	2	3	4	5	6	7	8	9	10	11	12	SALEABLE		34950-1210	34950-1220		
KEY D, STONE GRAY	33482-6264	D-SG	GCP	PLR	M-B	1	2	3	4	5	6	7	8	9	10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6265	A-BLK	GCP	PLR	M-B						6	7	8	9	10	11		SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6266	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7					12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6267	A-BLK	GCP	PLR	M-B			3	4	5	6	7						SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6268	A-BLK	GCP	PLR	M-B			3	4	5	6	7	8	9	10	11		SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6269	A-BLK	GCP	PLR	M-B	1	2	3	4	5			8	9	10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6270	A-BLK	GCP	PLR	M-B		2		4			7	8	9	10			SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6271	A-BLK	GCP	PLR	M-B		2					7	8	9				SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6272	A-BLK	GCP	PLR	M-B		2					7	8	9	10			SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6273	A-BLK	GCP	PLR	M-B								8					SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6274	A-BLK	GCP	PLR	M-B	1		3	4	5	6		8		10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6275	A-BLK	GCP	PLR	M-B				4				8		10			SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6276	A-BLK	GCP	PLR	M-B	1	2	3	4		6		8		10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6277	A-BLK	GCP	PLR	M-B	1	2	3								11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6278	A-BLK	GCP	PLR	M-B						6						12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6279	A-BLK	GCP	PLR	M-B	1	2	3	4	5		7	8	9	10	11		SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6280	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6			9				SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6281	A-BLK	GCP	PLR	M-B		2		4		6		8		10	11		SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6282	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6			9	10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6283	A-BLK	GCP	PLR	M-B						6			9	10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6284	A-BLK	GCP	PLR	M-B	1		3	4	5	6	7	8		10	11	12	SALEABLE		34950-1210	34950-1220		
KEY D, STONE GRAY	33482-6285	D-SG	GCP	PLR	M-B	1					6	7						SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6286	A-BLK	GCP	PLR	M-B		2	3					8	9				SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6287	A-BLK	GCP	PLR	M-B	1						7						SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6288	A-BLK	GCP	PLR	M-B	1					6							SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6289	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6		8					SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6290	A-BLK	GCP	PLR	M-B	1						7					12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6291	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7	8				12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6292	A-BLK	GCP	PLR	M-B									9				SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6293	A-BLK	GCP	PLR	M-B			3	4					9	10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6294	A-BLK	GCP	PLR	M-B	1	2			5	6	7	8					SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6295	A-BLK	GCP	PLR	M-B	1	2			5	6	7	8			11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6296	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7	8	9	10			SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6297	A-BLK	GCP	PLR	M-B				4		6				10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6298	A-BLK	GCP	PLR	M-B						6					11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6299	A-BLK	GCP	PLR	M-B	1	2					7	8					SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6300	A-BLK	GCP	PLR	M-B	1	2	3					8		10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6301	A-BLK	GCP	PLR	M-B	1	2					7	8				12	SALEABLE		34950-1210	34950-1220		
KEY B, LIGHT GRAY	33482-6302	B-LG	GCP	PLR	M-B										10	11		SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6303	A-BLK	GCP	PLR	M-B	1	2	3	4			7	8	9	10		12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6304	A-BLK	GCP	PLR	M-B	1	2	3	4			7	8	9	10			SALEABLE		34950-1210	34950-1220		
KEY B, LIGHT GRAY	33482-6305	B-LG	GCP	PLR	M-B										10	11	12	SALEABLE		34950-1210	34950-1220		
KEY B, LIGHT GRAY	33482-6306	B-LG	GCP	PLR	M-B	1	2	3	4	5	6	7			10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6307	A-BLK	GCP	PLR	M-B	1	2	3	4	5		7	8					SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6308	A-BLK	GCP	PLR	M-B							7	8	9	10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6309	A-BLK	GCP	PLR	M-B	1							8		10	11		SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6310	A-BLK	GCP	PLR	M-B	1			4							11		SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6311	A-BLK	GCP	PLR	M-B	1	2		4	5	6	7		9	10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6312	A-BLK	GCP	PLR	M-B								8	9				SALEABLE		34950-1210			



MX150 2X6 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS												STATUS	COMMENTS	OPTIONAL ATTATCHMENTS SOLD SEPERATELY			
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION														BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS		
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12						
KEY A, BLACK	33482-6313	A-BLK	GCP	PLR	M-B			3	4	5	6		8	9	10	11		SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6314	A-BLK	GCP	PLR	M-B			3			6	7	8	9	10			SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6315	A-BLK	GCP	PLR	M-B						6	7	8	9				SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6316	A-BLK	GCP	PLR	M-B					5	6	7	8			11		SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6317	A-BLK	GCP	PLR	M-B	1	2											SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6318	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7	8					SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6319	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7	8	9				SALEABLE		34950-1210	34950-1220		
KEY C, DARK GRAY	33482-6320	C-DG	GCP	PLR	M-B	1					6	7						SALEABLE		34950-1210	34950-1220		
KEY C, BROWN	33482-6321	C-BR	GCP	PLR	M-B	1	2	3	4	5	6							NOT RECOMMENDED	SEE 33482-6328	34950-1210	34950-1220		
KEY C, BROWN	33482-6322	C-BR	GCP	PLR	M-B	1	2			5	6							NOT RECOMMENDED	SEE 33482-6329	34950-1210	34950-1220		
KEY A, BLACK	33482-6323	A-BLK	GCP	PLR	M-B			3				7		9	10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6324	A-BLK	GCP	PLR	M-B			3						9	10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6325	A-BLK	GCP	PLR	M-B			3						9				SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6326	A-BLK	GCP	PLR	M-B					5	6	7			10	11		SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6327	A-BLK	GCP	PLR	M-B							7				11		SALEABLE		34950-1210	34950-1220		
KEY C, DARK GRAY	33482-6328	C-DG	GCP	PLR	M-B	1	2	3	4	5	6							SALEABLE		34950-1210	34950-1220		
KEY C, DARK GRAY	33482-6329	C-DG	GCP	PLR	M-B	1	2			5	6							SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6330	A-BLK	GCP	PLR	M-B	1	2	3	4					9	10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6331	A-BLK	GCP	PLR	M-B	1	2				6	7	8				12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6332	A-BLK	GCP	PLR	M-B				4	5		7	8	9	10			SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6333	A-BLK	GCP	PLR	M-B				4					9	10			SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6334	A-BLK	GCP	PLR	M-B				4	5			8		10			SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6335	A-BLK	GCP	PLR	M-B	1	2		4	5	6	7					12	SALEABLE		34950-1210	34950-1220		
KEY A, YELLOW	33482-6336	A-YL	GCP	PLR	M-B													SALEABLE		34950-1210	34950-1220		
KEY B, LIGHT GRAY	33482-6337	B-LG	GCP	PLR	M-B					5			8					SALEABLE		34950-1210	34950-1220		
KEY B, LIGHT GRAY	33482-6338	B-LG	GCP	PLR	M-B						5		8			11	12	SALEABLE		34950-1210	34950-1220		
KEY B, LIGHT GRAY	33482-6339	B-LG	GCP	PLR	M-B			3	4	5			8	9	10	11	12	SALEABLE		34950-1210	34950-1220		
KEY B, LIGHT GRAY	33482-6340	B-LG	GCP	PLR	M-B	1	2	3	4	5			8	9	10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6341	A-BLK	GCP	PLR	M-B	1	2	3		5				9		11		SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6342	A-BLK	GCP	PLR	M-B		2	3		5						11		SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6343	A-BLK	GCP	PLR	M-B	1	2	3						9		11		SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6344	A-BLK	GCP	PLR	M-B	1	2	3	4	5				9		11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6345	A-BLK	GCP	PLR	M-B		2	3	4	5						11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6346	A-BLK	GCP	PLR	M-B	1												SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6347	A-BLK	GCP	PLR	M-B	1	2	3										SALEABLE		34950-1210	34950-1220		
KEY B, LIGHT GRAY	33482-6348	B-LG	GCP	PLR	M-B	1	2	3	4		6					11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6349	A-BLK	GCP	PLR	M-B				4			7	8					SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6350	A-BLK	GCP	PLR	M-B		2						8					SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6351	A-BLK	GCP	PLR	M-B		2		4				8		10			SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6352	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6		8		10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6353	A-BLK	GCP	PLR	M-B	1					6	7	8				12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6354	A-BLK	GCP	PLR	M-B		2	3	4		6		8		10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6355	A-BLK	GCP	PLR	M-B		2				6	7	8		10	11		SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6356	A-BLK	GCP	PLR	M-B	1	2	3	4		6			9	10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6357	A-BLK	GCP	PLR	M-B					5			8					SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6358	A-BLK	GCP	PLR	M-B				4						10			SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6359	A-BLK	GCP	PLR	M-B				4			7	8	9	10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6360	A-BLK	GCP	PLR	M-B					5	6		8	9	10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6361	A-BLK	GCP	PLR	M-B				4	5	6		8	9	10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6362	A-BLK	GCP	PLR	M-B	1	2	3		5	6	7	8	9		11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6363	A-BLK	GCP	PLR	M-B				4	5		7	8	9	10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6364	A-BLK	GCP	PLR	M-B				4			7		9	10			SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6365	A-BLK	GCP	PLR	M-B						6	7	8	9	10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6366	A-BLK	GCP	PLR	M-B	1	2				6	7				11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6367	A-BLK	GCP	PLR	M-B					5			8		10			SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6368	A-BLK	GCP	PLR	M-B	1	2	3	4			7	8	9	10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6369	A-BLK	GCP	PLR	M-B				4									SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6370	A-BLK	GCP	PLR	M-B	1	2	3			6	7			10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6371	A-BLK	GCP	PLR	M-B							7	8			11		SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6372	A-BLK	GCP	PLR	M-B	1		3		5			8		10		12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6373	A-BLK	GCP	PLR	M-B		2		4		6	7		9		11		SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6374	A-BLK	GCP	PLR	M-B		2								10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6375	A-BLK	GCP	PLR	M-B							7		9	10			SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6376	A-BLK	GCP	PLR	M-B		2		4			7						SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6377	A-BLK	GCP	PLR	M-B	1	2	3	4		6			9	10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6378	A-BLK	GCP	PLR	M-B	1		3		5						11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6379	A-BLK	GCP	PLR	M-B	1		3		5			8		10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6380	A-BLK	GCP	PLR	M-B		2					7	8					SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6381	A-BLK	GCP	PLR	M-B		2		4			7	8					SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6382	A-BLK	GCP	PLR	M-B				4	5	6		8		10	11		SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6383	A-BLK	GCP	PLR	M-B	1	2	3	4			7	8	9	10	11		SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6384	A-BLK	GCP	PLR	M-B			3	4					9	10			SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6385	A-BLK	GCP	PLR	M-B			3	4							11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6386	A-BLK	GCP	PLR	M-B	1	2	3	4		6	7	8	9	10	11		SALEABLE		34			



MX150 2X6 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS												STATUS	COMMENTS	OPTIONAL ATTATCHMENTS SOLD SEPERATELY			
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION														BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS		
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12						
KEY A, BLACK	33482-6461	A-BLK	GCP	PLR	M-B		2			5	6	7	8			11		SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6462	A-BLK	GCP	PLR	M-B		2	3		5	6	7	8	9		11		SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6463	A-BLK	GCP	PLR	M-B	1	2		4	5	6	7				11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6464	A-BLK	GCP	PLR	M-B	1	2		4	5	6	7	8		10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6465	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7		9		11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6466	A-BLK	GCP	PLR	M-B												12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6467	A-BLK	GCP	PLR	M-B		2	3	4									SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6468	A-BLK	GCP	PLR	M-B				4	5			8		10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6469	A-BLK	GCP	PLR	M-B	1								9	10			SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6470	A-BLK	GCP	PLR	M-B							7	8	9			12	SALEABLE		34950-1210	34950-1220		
KEY C, DARK GRAY	33482-6471	C-DG	GCP	PLR	M-B			3	4				8					SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6472	A-BLK	GCP	PLR	M-B	1	2					7	8	9	10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6473	A-BLK	GCP	PLR	M-B					5	M-B	7	8	9		11		SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6474	A-BLK	GCP	PLR	M-B	1	2			5					10		12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6475	A-BLK	GCP	PLR	M-B					5								SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6476	A-BLK	GCP	PLR	M-B			3	4	5								SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6477	A-BLK	GCP	PLR	M-B	1	2			5				9	10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6478	A-BLK	GCP	PLR	M-B					5				9		11		SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6479	A-BLK	GCP	PLR	M-B	1							8			11		SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6480	A-BLK	GCP	PLR	M-B	1			4	5	6	7						SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6481	A-BLK	GCP	PLR	M-B	1			4	5	6	7	8			11		SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6482	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7	8			11		SALEABLE		34950-1210	34950-1220		
KEY B, LIGHT GRAY	33482-6483	B-LG	GCP	PLR	M-B	1					6	7			10	11	12	SALEABLE		34950-1210	34950-1220		
KEY B, LIGHT GRAY	33482-6484	B-LG	GCP	PLR	M-B	1					6	7	8	9	10	11	12	SALEABLE		34950-1210	34950-1220		
KEY B, LIGHT GRAY	33482-6485	B-LG	GCP	PLR	M-B	1				5	6	7	8	9	10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6486	A-BLK	GCP	PLR	M-B	1	2			5		7	8	9	10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6487	A-BLK	GCP	PLR	M-B							7				11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6488	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7	8			11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6489	A-BLK	GCP	PLR	M-B			3				7	8			11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6490	A-BLK	GCP	PLR	M-B	1	2	3	4							11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6491	A-BLK	GCP	PLR	M-B	1		3		5		7		9				SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6492	A-BLK	GCP	PLR	M-B		2				6	7	8					SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6493	A-BLK	GCP	PLR	M-B					5		7		9	10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6494	A-BLK	GCP	PLR	M-B					5				9	10	11		SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6495	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6		8	9	10	11		SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6496	A-BLK	GCP	PLR	M-B	1	2	3	4		6	7	8	9			12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6497	A-BLK	GCP	PLR	M-B							7		9			12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6498	A-BLK	GCP	PLR	M-B	1	2		4	5	6	7	8	9			12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6499	A-BLK	GCP	PLR	M-B			3						9	10	11		SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6500	A-BLK	GCP	PLR	M-B		2			5		7			10			SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6501	A-BLK	GCP	PLR	M-B				4			7						SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6502	A-BLK	GCP	PLR	M-B				4		6	7						SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6503	A-BLK	GCP	PLR	M-B						6	7	8					SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6504	A-BLK	GCP	PLR	M-B		2	3	4	5	6		8	9	10	11	12	SALEABLE		34950-1210	34950-1220		
KEY B, LIGHT GRAY	33482-6505	B-LG	GCP	PLR	M-B					5			8	9	10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6506	A-BLK	GCP	PLR	M-B								8	9			12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6507	A-BLK	GCP	PLR	M-B	1	2		4	5	6		8					SALEABLE		34950-1210	34950-1220		
KEY A, YELLOW	33482-6508	A-YL	GCP	PLR	M-B			3			6	7	8	9	10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6509	A-BLK	GCP	PLR	M-B				4	5		7	8			11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6510	A-BLK	GCP	PLR	M-B							7	8			11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6511	A-BLK	GCP	PLR	M-B								8			11	12	SALEABLE		34950-1210	34950-1220		
KEY B, LIGHT GRAY	33482-6512	B-LG	GCP	PLR	M-B	1		3		5	6	7			10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6513	A-BLK	GCP	PLR	M-B	1		3						9			12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-6514	A-BLK	GCP	PLR	M-B	1	2		4	5	6	7	8					SALEABLE		34950-1210	34950-1220		
KEY B, LIGHT GRAY	33482-6515	B-LG	GCP	PLR	M-B								8					SALEABLE		34950-1210	34950-1220		
KEY B, LIGHT GRAY	33482-6516	B-LG	GCP	PLR	M-B											11		SALEABLE		34950-1210	34950-1220		

MX150 2X8 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS																STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY					
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION																		BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	90° ADAPTOR WITH RIBS	90° ADAPTOR WITHOUT RIBS		
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16								
KEY A, BLACK	33482-8640	A-BLK	GCP	PLR	M-B					5											16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641		
KEY A, BLACK	33482-8641	A-BLK	GCP	PLR	M-B					5												SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641		
KEY B, LIGHT GRAY	33482-8642	B-LG	GCP	PLR	M-B				4		6	7	8					12		14		SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641		
KEY A, BLACK	33482-8643	A-BLK	GCP	PLR	M-B															15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641		
KEY B, LIGHT GRAY	33482-8644	B-LG	GCP	PLR	M-B				4													SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641		
KEY B, LIGHT GRAY	33482-8645	B-LG	GCP	PLR	M-B				4		6	7	8									SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641		
KEY A, BLACK	33482-8646	A-BLK	GCP	PLR	M-B				4		6	7	8					12				SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641		
KEY A, BLACK	33482-8647	A-BLK	GCP	PLR	M-B																16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641		
KEY A, BLACK	33482-8648	A-BLK	GCP	PLR	M-B				4									12				SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641		
KEY B, LIGHT GRAY	33482-8649	B-LG	GCP	PLR	M-B																16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641		
KEY B, LIGHT GRAY	33482-8650	B-LG	GCP	PLR	M-B				4									12		14		SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641		
KEY B, LIGHT GRAY	33482-8651	B-LG	GCP	PLR	M-B															14		SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641		
KEY B, LIGHT GRAY	33482-8652	B-LG	GCP	PLR	M-B						6	7	8							14		SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641		
KEY A, BLACK	33482-8653	A-BLK	GCP	PLR	M-B									9						15		SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641		
KEY A, BLACK	33482-8654	A-BLK	GCP	PLR	M-B				4				8					12				SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641		
KEY B, LIGHT GRAY	33482-8655	B-LG	GCP	PLR	M-B				4				8					12		14		SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641		
KEY B, LIGHT GRAY	33482-8656	B-LG	GCP	PLR	M-B								8							14		SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641		
KEY A, BLACK	33482-8657	A-BLK	GCP	PLR	M-B	1						7										SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641		
KEY B, LIGHT GRAY	33482-8658	B-LG	GCP	PLR	M-B				4		6	7	8					12		14		SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641		
KEY B, LIGHT GRAY	33482-8659	B-LG	GCP	PLR	M-B				2		6	7	8							14		SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641		
KEY B, LIGHT GRAY	33482-8660	B-LG	GCP	PLR	M-B				2				8							14		SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641		
KEY A, BLACK	33482-8661	A-BLK	GCP	PLR	M-B				2				8					12				SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641		
KEY B, LIGHT GRAY	33482-8662	B-LG	GCP	PLR	M-B				2				8					12		14		SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641		
KEY A, BLACK	33482-8663	A-BLK	GCP	PLR	M-B				2				8									SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641		
KEY A, BLACK	33482-8664	A-BLK	GCP	PLR	M-B					3			8		10	11				15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641		
KEY A, BLACK	33482-8665	A-BLK	GCP	PLR	M-B					3	4	5	6	7	8	10	11				15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8666	A-BLK	GCP	PLR	M-B				2			6	7	8		10			13	14	15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8667	A-BLK	GCP	PLR	M-B				2			5	6			10			13	14	15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8668	A-BLK	GCP	PLR	M-B				2			5	6			10	11		13	14	15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8669	A-BLK	GCP	PLR	M-B				2				6			10			13	14			SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8670	A-BLK	GCP	PLR	M-B				2							10						SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641		
KEY A, BLACK	33482-8671	A-BLK	GCP	PLR	M-B				2			4	5	6		10	11		12	13	14		SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8672	A-BLK	GCP	PLR	M-B						4					10			12	13	14		SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8673	A-BLK	GCP	PLR	M-B				2				6	7	8								SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8674	A-BLK	GCP	PLR	M-B				2				5	6									SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8675	A-BLK	GCP	PLR	M-B				2				5	6			11						SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8676	A-BLK	GCP	PLR	M-B							5	6	7	8				13				SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8677	A-BLK	GCP	PLR	M-B							5	6	7	8		11		13				SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8678	A-BLK	GCP	PLR	M-B							5	6	7	8				12	13	14		SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8679	A-BLK	GCP	PLR	M-B							5	6	7	8		11		12	13	14		SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8680	A-BLK	GCP	PLR	M-B							5	6	7	8		11		12	13	14		SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8681	A-BLK	GCP	PLR	M-B								7								15		SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8682	A-BLK	GCP	PLR	M-B																15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8683	A-BLK	GCP	PLR	M-B																15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8684	A-BLK	GCP	PLR	M-B	1		2	3	4	5	6		8					13		15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8685	A-BLK	GCP	PLR	M-B														13	14	15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8686	A-BLK	GCP	PLR	M-B									8					13	14	15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8687	A-BLK	GCP	PLR	M-B								7	8		11		12	13	14	15		SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8688	A-BLK	GCP	PLR	M-B								7	8				12	13	14	15		SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8689	A-BLK	GCP	PLR	M-B								7	8		11			13				SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8690	A-BLK	GCP	PLR	M-B								7	8					13				SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8691	A-BLK	GCP	PLR	M-B							5											SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8692	A-BLK	GCP	PLR	M-B				2						9	10					15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8693	A-BLK	GCP	PLR	M-B				2							10					15		SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8694	A-BLK	GCP	PLR	M-B								5	6	7	8	9			12			SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8695	A-BLK	GCP	PLR	M-B				2				5	6	7	8			10		12		SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33																												

