

|                             |                                                                                                                                       |
|-----------------------------|---------------------------------------------------------------------------------------------------------------------------------------|
| Producer                    | Qoltec                                                                                                                                |
| Power                       | 75W                                                                                                                                   |
| Input voltage               | 220 – 240 V                                                                                                                           |
| Output voltage              | 12V                                                                                                                                   |
| Battery voltage             | 12V                                                                                                                                   |
| Type of charging            | 6 step charging mode                                                                                                                  |
| Battery capacity            | 4Ah-80Ah                                                                                                                              |
| Charging time               | Depending on battery capacity                                                                                                         |
| Connector                   | Red + black crocodile type terminals                                                                                                  |
| Cooling system              | 1 x Fan                                                                                                                               |
| Protection                  | Reverse polarity protection<br>Overvoltage protection<br>Short-circuit protection<br>Overcurrent protection<br>Low voltage protection |
| Cable length                | 0.59m                                                                                                                                 |
| Power cord length           | 0.34m                                                                                                                                 |
| Usage                       | Maintenance-free batteries:<br>VRLA : AGM/GEL/SLA                                                                                     |
| Notices                     | No repair function<br>Does not charge LiFePO4 batteries                                                                               |
| OTHER PARAMETERS            |                                                                                                                                       |
| Colour                      | Black                                                                                                                                 |
| Material                    | Plastic                                                                                                                               |
| Operating temperature       | -20°C ~ +40°C                                                                                                                         |
| Dimensions (D/L x W x H)    | 50 x 152 x 70mm                                                                                                                       |
| Package                     | Box                                                                                                                                   |
| Package contents            | 1 x Charger<br>1 x Warranty card<br>1 x Operating instructions                                                                        |
| Package depth / length [mm] | 110                                                                                                                                   |
| Package width [mm]          | 203                                                                                                                                   |
| Package height [mm]         | 55                                                                                                                                    |
| Net weight [kg]             | 0.262                                                                                                                                 |
| Gross weight [kg]           | 0.306                                                                                                                                 |
| Certificate                 | CE                                                                                                                                    |
| Warranty                    | 24 month                                                                                                                              |
| EAN code                    | 5901878524955                                                                                                                         |