

Cable USB 2.0 Micro-B female panel-mount > USB 2.0 Micro-B male 1 m

Description

This cable by Delock can be used to extend a USB 2.0 connection and to connect various devices. The female ports can be attached with two screws, e.g. to a slot bracket, a cable duct or an enclosure with the corresponding opening. In this way, it is possible to install a USB connector in an easily accessible position.



Item no. 85246

EAN: 4043619852468

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x USB 2.0 Type Micro-B female with screw nuts for installation >
 - 1 x USB 2.0 Type Micro-B male
- Screw type: #4-40 UNC
- Mounting hole Type Micro-B ca. 8 x 3 mm, screw hole pitch ca. 30 mm
- Data transfer rate up to 480 Mbps
- Cable gauge:
 - 28 AWG data line
 - 28 AWG power line
- Cable diameter: ca. 3.8 mm
- Colour: black
- Length incl. connectors: ca. 1 m

System requirements

- A free USB port

Package content

- USB panel-mount cable
- 2 screws

Images



Interface

Connector 1:	1 x USB 2.0 Type Micro-B female
Connector 2:	1 x USB 2.0 Type Micro-B male

Technical characteristics

Data transfer rate:	USB 2.0 up to 480 Mb/s
---------------------	------------------------

Physical characteristics

Cable gauge:	28 AWG data line 28 AWG power line
Length:	1 m
Colour:	black
Cable diameter:	3.8 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de