

USB Type-C™ Triple Display Docking Station with DisplayLink® 4K / USB Hub / LAN / SD / Audio / PD 96 W

Description

This docking station by Delock can be connected to a computer with a USB-C™ DP Alt Mode, Thunderbolt™ 3 or Thunderbolt™ 4 and provides a variety of interfaces. **Three monitors** can be operated at the monitor outputs at the same time. **Five built-in USB ports** allow the use of peripherals and another USB port can be used to charge mobile devices. Connectors for a **microphone** and **speaker**, a **Gigabit network** connection, as well as a card reader for **SD** memory cards complete the features.

Triple Display 4K UHD resolution

When using the three video outputs at the same time, one monitor is operated via DisplayPort Alternate Mode, the other two via **DisplayLink®**. One port can be used from each double group of DisplayPort and HDMI connector. The Delock docking station can also be operated on devices without a USB Type-C™ port with DP Alt Mode support, with a video output on a maximum of two monitors. A maximum resolution of **4K** on all ports can be guaranteed, regardless of the operating system. Due to the DisplayLink® graphics chipset it is possible to use mirrored and extended screen functions on Windows and Mac OS operating systems.

USB Power Delivery (USB PD 3.0) support up to 96 watt

Via the power supply, which is connected to the docking station, the host device is charged with up to 96 watts during operation.

Stand

Due to the **vertical installation**, the Delock docking station takes up less space on the desk.



Item no. 88051

EAN: 4043619880515

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
1 x USB Type-C™ female

- 1 x DisplayPort female (DP Alt Mode)
- 2 x DisplayPort female (DisplayLink®)
- 1 x HDMI female (DP Alt Mode)
- 2 x HDMI female (DisplayLink®)
- 4 x USB 5 Gbps Type-A female
- 1 x USB 10 Gbps USB Type-C™ female
- 1 x microphone 3.5 mm stereo jack
- 1 x speaker 3.5 mm stereo jack
- 1 x Gigabit LAN 10/100/1000 Mbps RJ45 jack
- 1 x SD slot
- 1 x DC 20 V power connector
- Maximum resolution (depending on the system and the connected hardware):
 - Host USB Type-C™ DP Alt Mode: 3 x 4K / 60 Hz
 - Host without DP Alt Mode: 2 x 4K / 60 Hz
- Transmission of audio and video signals
- Functions: Mirrored or Extended
- Input power: 135 W, 39 W are used for the docking station
- Output power for host: max. 96 W
- 1 x LED indicator
- Colour: black
- Dimensions without stand (LxWxH): ca. 195 x 94 x 35 mm

Power supply specification

- Wall power supply
- Input: AC 100 ~ 240 V / 50 ~ 60 Hz / 2.37 A
- Output: 20 V / 6.75 A / 135 W
- Ground outside, plus inside
- Dimensions:
 - inside: ø ca. 2.5 mm
 - outside: ø ca. 5.5 mm
 - length: ca. 10.0 mm

System requirements

- Mac OS 12.4 or above
- Windows 10/10-64/11
- A free USB Type-C™ female port (DisplayLink®) or
- Device with a free USB Type-C™ port and DisplayPort alternate mode or with a free Thunderbolt™ 3 or Thunderbolt™ 4 port

Package content

- USB docking station
- Cable USB-C™ male to USB-C™ male, length ca. 1 m
- Power supply, cable length ca. 1.6 m

- Power cord, length ca. 1.8 m
- User manual

Images



Maximum resolution (depending on the system and the connected hardware)

Host Type-C™ DP Alt Mode:		
Single Display	HDMI	1 x 3840 x 2160 @ 60Hz
	DP	1 x 3840 x 2160 @ 60Hz
Dual Display	HDMI + HDMI	2 x 3840 x 2160 @ 60Hz
	HDMI + DP	2 x 3840 x 2160 @ 60Hz
Triple Display	HDMI + HDMI + HDMI (DP Alt Mode)	3 x 3840 x 2160 @ 60Hz
	HDMI + HDMI + DP (DP Alt Mode)	3 x 3840 x 2160 @ 60Hz
	HDMI + DP + DP (DP Alt Mode)	3 x 3840 x 2160 @ 60Hz
Host without DP Alt Mode:		
Single Display	HDMI (Display, Audio)	1 x 3840 x 2160 @ 60Hz
	DP (Display, Audio)	1 x 3840 x 2160 @ 60Hz
Dual Display (BT)	HDMI (Display, Audio) + HDMI (Display, Audio)	2 x 3840 x 2160 @ 60Hz
	DP (Display, Audio) + DP (Display, Audio)	2 x 3840 x 2160 @ 60Hz



General

Function:	mirror and extend
Supported operating system:	Windows 10 32-Bit Windows 10 64-Bit Windows 11 Mac OS 12.4 oder höher

Technical characteristics

Maximum screen resolution:	3840 x 2160 @ 60 Hz
----------------------------	---------------------

Physical characteristics

Length:	195 mm
Width:	94 mm
Height:	35 mm
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de