

Antenna Cable SMA plug > SMA jack CFD400 LLC400

0.4 m low loss

Description

This high-quality coaxial cable ensures a reliable connection of components of the radio frequency technology. It is characterised by a very low attenuation.



Item no. 13004

EAN: 4043619130047

Country of origin: Taiwan,
Republic of China

Package: Box

Technical details

- Connector: SMA plug > SMA jack
- Cable type: CFD400, LLC400
- Impedance: 50 Ohm
- Cable Attenuation:
 - 2.4 GHz: ca. 0.22 dB per meter
 - 5.7 GHz: ca. 0.35 dB per meter
- Diameter: ca. 10.5 mm
- Smallest bending radius: 51.5 mm
- Colour: black
- Cable length: ca. 0.4 m


System requirements

- Device with a free SMA connector

Package content

- Antenna cable

Images



Interface

Connector 1:	1 x SMA plug
Connector 2:	1 x SMA jack

Physical characteristics

Cable category:	coaxial
Cable type:	CFD400, LLC400
Cable attenuation:	0.22 dB @ 2.4 GHz per meter
Cable colour:	black
Cable length incl. connectors:	0.4 m
Smallest bending radius:	51.5 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

