

USB 10 Gbps 2 Port USB Type-A + 2 Port USB Type-C™ Hub with USB Type-C™ connector and PD 95 Watt

Description

This solid USB hub by Delock with **metal housing** can be connected to a computer, laptop or mobile device via the **USB Type-C™** interface. It has **two USB Type-A connectors as well as two USB Type-C™ connectors**. Different USB devices such as USB flash memory, card reader, external enclosure etc. can be connected.

USB Power Delivery (USB PD 3.0) support up to 95 watt

This hub has a **USB Type-C™ Power Delivery port**. If this port is connected to the power supply of the laptop or tablet, the host device is charged with up to 95 watts during operation.

Small, stable and handy

Due to its **small dimensions and its sturdy housing**, this Delock hub is particularly suitable for travelling. It can simply be packed into the bag together with the laptop or tablet and used as needed.



Item no. 64302

EAN: 4043619643028

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB 10 Gbps USB Type-C™ male
 - 2 x USB 10 Gbps USB Type-C™ female
 - 2 x USB 10 Gbps Type-A female
 - 1 x USB Type-C™ Power Delivery female
- Chipset: Genesys Logic GL3590
- Data transfer rate up to 10 Gbps
- Bootable
- Electrical power (depends on host, distribution of total power to individual ports):
 - total: max. 15 watt (5 V / 3 A)
 - USB Type-C™: max. 10 watt (5 V / 2 A)
 - USB Type-A: max. 4.5 watt (5 V / 0.9 A)
- Input power PD: 100 W, 5 W are used for the hub
- Output power PD for host: max. 95 W
- 1 x LED indicator
- Robust metal housing
- Cable length: ca. 15 cm
- Colour: grey
- Plug & Play
- Dimensions (LxWxH): ca. 102 x 31 x 11 mm

System requirements

- Android 14.0 or above
- Chrome OS
- Linux Kernel 6.5 or above
- Mac OS 14.2.1 or above
- Windows 10/10-64/11
- iPad Air (4th Generation) or above
- iPad Pro (3rd Generation) or above
- Surface Pro 7
- Device with a free USB Type-C™ port or with a free Thunderbolt™ 3 or Thunderbolt™ 4 port

Package content

- Hub USB 10 Gbps
- User manual

Images



General

Function:	Plug & Play
Supported operating system:	Chrome OS Surface Pro 7 Windows 10 32-Bit Windows 10 64-Bit iPad Pro (3rd Generation) or above iPad Air (4th Generation) or above Windows 11 Android 14.0 or above Linux Kernel 6.5 or above Mac OS 14.2.1 or above
LED indicator:	1 x

Interface

Connector 1:	1 x USB 10 Gbps USB Type-C™ male
Connector 2:	2 x USB 10 Gbps USB Type-C™ female
Connector 3:	2 x USB 10 Gbps Type-A female
Connector 4:	1 x USB Type-C™ Power Delivery female

Technical characteristics

Chipset:	Genesys Logic GL3590
Data transfer rate:	10 Gbps

Physical characteristics

Cable length:	15 cm
Length:	102 mm
Width:	31 mm
Height:	11 mm
Colour:	grey

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de