



BETA 7341V
RENEGADE woven fabric,
hard-wearing and breathable,
green details



Certifications and Standards

CE S1PS FO SR HRO EN ISO 20345:2022

Features

The 7341V safety footwear focuses on breathability, comfort and design, ensuring wellbeing and style throughout the working day.

SAFETY WITH STYLE

The shoe that offers protection without sacrificing looks.

Thanks to the "urban" style, inspired by sports shoes, it is also perfect to wear after work.

EXTREME COMFORT

Renegade combines advanced cushioning and superior support to provide exceptional comfort throughout the working day.

Thanks to its innovative design and high performance, it ensures a smooth and comfortable walk.

WIDE FOOTBED

Wide fit design further improves shoe comfort, avoiding possible constriction of the foot at any time of day

BREATHABLE AND RESISTANT

The woven fabric upper, thanks to its open structure, offers exceptional lightness and optimal breathability. Its remarkable durability makes it perfect for ensuring a long life without compromising on quality.



INNOVATIVE DESIGN

The 7341V shoe combines sporty design and modern style, highlighting an innovative outsole that ensures safety and comfort with every step



TRADITIONAL LACING

With traditional lacing, the laces can be adjusted for a secure and customised fit, ensuring perfect comfort with every step.



MAXIMUM RESISTANCE

The rubber outsole makes the shoe extremely durable and heat-resistant up to 300°C.



Certifications and Standards

CE S1PS FO SR HRO EN ISO 20345:2022



Specifications

LACING:	traditional
WEIGHT (INDICATIVE SIZE 42):	495 g
TYPE:	low

Lightness

- Hard-wearing, ultrabreathable woven fabric with TPU (thermoplastic polyurethane) inserts
- Heel stability support
- Traditional lacing

Comfort

- EVA (ethylene vinyl acetate) midsole
- Durable nitrile rubber tread



Safety

EVA FOAM underfoot cover

Protections

Tip: Polymer material, 200 joules
Durability: Composite fibre, ceramic treatment

Coded items

	Art.	EU	UK	 mm
073410537	7341V 37	37	4,5	248
073410538	7341V 38	38	5	254
073410539	7341V 39	39	6	261
073410540	7341V 40	40	6,5	268
073410541	7341V 41	41	7	274
073410542	7341V 42	42	8	281
073410543	7341V 43	43	9	288
073410544	7341V 44	44	10	294
073410545	7341V 45	45	10,5	301
073410546	7341V 46	46	11	308
073410547	7341V 47	47	12	314
073410548	7341V 48	48	13	321

Scan the QR Code to access the web tab

Specs, media and documentation in one click.

