

42MP

combination wrenches, open and offset ring ends, bright chrome-plated

DIN 3113 UNI-ISO 7738

- Compact heads.
- Torque values significantly higher than ISO 1711-1 standards

	art.	 mm	L mm	A mm	Ø mm	S1 mm	S2 mm	 g
000421606	42MP 6	6x6	100	16,5	10,7	3,8	5,1	15
000421607	42MP 7	7x7	110	18,2	11,5	3,7	5,2	17
000421608	42MP 8	8x8	120	20,2	13,2	4,1	5,5	23
000421609	42MP 9	9x9	130	22,3	14,7	4,2	6,8	30
000421610	42MP 10	10x10	140	23,6	16,2	4,8	7,0	38
000421611	42MP 11	11x11	150	25,7	17,7	5,0	6,9	44
000421612	42MP 12	12x12	158	27,2	18,6	5,0	7,2	52
000421613	42MP 13	13x13	170	28,9	21,0	5,8	8,5	70
000421614	42MP 14	14x14	178	32,0	22,2	5,9	8,9	85
000421615	42MP 15	15x15	190	34,4	23,6	6,2	9,1	97
000421616	42MP 16	16x16	199	36,5	24,9	6,2	9,4	108
000421617	42MP 17	17x17	209	38,8	26,3	6,5	9,9	122
000421618	42MP 18	18x18	219	39,5	27,7	7,1	10,8	142
000421619	42MP 19	19x19	230	42,2	28,8	7,5	10,8	160
000421620	42MP 20	20x20	240	42,7	30,0	7,5	11,2	180
000421621	42MP 21	21x21	250	45,5	31,5	7,5	11,8	192
000421622	42MP 22	22x22	260	48,50	34,0	8,0	12,5	210
000421624	42MP 24	24x24	280	50,50	35,0	8,0	13,0	250
000421627	42MP 27	27x27	307	55,0	40,4	9,1	15,0	440
000421630	42MP 30	30x30	337	60,0	43,7	9,8	16,0	473
000421632	42MP 32	32x32	360	65,0	47,7	10,8	17,2	500

