External Industry Hub 4 x USB 5 Gbps Type-A with 20 kV ESD protection

Description

This solid industry capable USB hub by Delock can be connected to a computer via the USB Type-A interface. It expands the computer by four USB Type-A connectors, which supports the USB Battery Charging specification BC1.2. Thus, connected devices such as smartphones can be charged faster. If necessary, an optional power supply or an optional power cable can be connected to the power socket.



Item no. 63309

EAN: 4043619633098

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
  1 x USB 5 Gbps Type-B female >
  4 x USB 5 Gbps Type-A female - Battery Charging specification BC1.2
  1 x 9 – 40 V DC jack
  1 x 3 pin terminal power connector
- Chipset: VIA VL817
- Data transfer rate up to:
  SuperSpeed USB 5 Gbps,
  Hi-Speed 480 Mbps,
  Full-Speed 12 Mbps,
  Low-Speed 1.5 Mbps
- 5 x LED indicator
- USB ports with screw holes
- Robust metal housing
- Pitch of screw hole USB Type-A: ca. 19 mm
- Pitch of screw hole USB Type-B: ca. 16.5 mm
- Thread size: M3
- Removable wall-mount brackets
- Power supply: Bus-powered or Self-powered
- Flexible power supply with 9 V to 40 V
- Automatic detection of the input polarity of the power connectors
- ESD protection up to 20 kV for all ports
- Dimensions (LxWxH): ca. 158 x 80 x 32 mm

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

- Colour: black
- Plug & Play

Specification of power connector

- 9 - 40 V
- Dimensions:
  inside: ø ca. 2.1 mm
  outside: ø ca. 5.5 mm
  length: ca. 9 mm

System requirements

- Linux Kernel 3.16 or above
- Mac OS 10.9 or above
- Windows 7/7-64/8.1/8.1-64/10/10-64/11
- PC or laptop with a free USB Type-A port


Package content

- Hub USB
- 1 x cable USB A male to USB B male, length ca. 1 m
- 2 x wall mounting brackets
- 1 x DIN rail mounting: 35 mm
- 1 x 3 pin terminal block
- User manual

Images







All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

Allgemein

Funktion:	Battery Charging BC1.2 Plug & Play
Montageart:	Hutschiene Schraubmontage
Unterstütztes Betriebssystem:	Linux Kernel 3.16 oder höher Mac OS 10.9 oder höher Windows 10 32-Bit Windows 7 32-Bit Windows 7 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit Windows 11
LED Anzeige:	5 x

Schnittstelle

Anschluss 1:	1 x USB 5 Gbps Typ-B Buchse
Anschluss 2:	4 x USB 5 Gbps Typ-A Buchse - Battery Charging Spezifikation BC1.2
Anschluss 3:	1 x 9 – 40 V DC Strombuchse
Anschluss 4:	1 x 3 Pin Terminal Stromanschluss

Technische Eigenschaften

Datentransferrate:	5 Gbps

Physikalische Eigenschaften

Länge:	158 mm
Breite:	80 mm
Höhe:	32 mm
Farbe:	schwarz

Manufacturer information

Street	Beeskowdamm 13/15

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**