

Eaton 80NHG01B

Catalog Number: 80NHG01B

Eaton Bussmann series low voltage NH Fuse, Live gripping lug, 500V, 80A, 120 kAIC, Combination fuse status indicator, Fuse, Blade end connection, Class C gL/gG, Square-body with knife blade contact, Ceramic body

General specifications

Product Name	Catalog Number
Eaton Bussmann series low voltage NH Fuse	80NHG01B
Packing Unit	
Pack	
Case Pack	
Quantity	
3	
36	
Length	
137 mm	
325 mm	
Height	
68 mm	
155 mm	
ERP Name	
SAP-UNITY	
SAP-UNITY	
Product Height	
58 mm	
Product Weight	
270.667 g	

Product Length/Depth	
135 mm	
Product Width	
30 mm	



Compliances

CE Marked

Certifications

IEC 60269-1

Electrical data

Amperage Rating

80 A

Voltage rating

500 V

Voltage type

AC

Breaking capacity

120 kA

Frequency rating - min

45 Hz

Frequency rating - max

62 Hz

Product specification

DIN 43620

Fuse size

NH01

Insulated metal gripping lugs (IMGL)

No

Accessories

Suitable for

Microswitch 170H0235

Do pobrania



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. Wszelkie
prawa zastrzeżone.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia