
Receptacle

KS-215 M1.6 E05


Item KS-215M1.6E05

GO TO PRODUCT

Partner for Future Technology







General data

Product group:	Receptacles (KS)
Series:	KS-215
Sub-series:	KS-215 M screw-in version
Type of receptacle connection:	Plug / open
Press ring:	No
Surface area:	Gold
Collar diameter:	2.2 mm [.086 in]
Collar height:	5 mm [.196 in]
Knurl:	No
Vacuum-tight:	No
RoHS-compliant:	RoHS-3;6c

Mounting hole

Mounting hole in CEM1:	1.99 mm [.078 in]
Mounting hole in FR4:	1.99 mm [.078 in]

Mechanical data

Total length:	29.5 mm [1.16 in]
Outer diameter:	2 mm [.078 in]

INGUN Prüfmittelbau GmbH
Max-Stromeyer-Straße 162
78467, Constance, Germany
Phone +49 7531 8105-0
Customer hotline +49 7531 8105-888
Fax +49 7531 8105-65
info@ingun.com

Learn more about
Test probes

RECEPTACLES

Prices and delivery times on request.
Technical changes reserved. 04/24_GB

ingun.com