






Screw in Bulk
Ø 3*16



Rating	Input:12V/24 DC Output:USB Socket - 5V 2.1A max. Auto Sockets - 20A max.
Insulation Resistance	DC 500V 100MΩ Min.
Dielectric Strength	AC 1500V 1 minute
Operating Temperature	-20℃~60℃

Remarks:

- 1.Electric Parameter Output Tolerances $\pm 5\%$
Unless Otherwise Specified
- 2.Tolerances ± 0.3 Unless Otherwise Specified

客戶編號: ET061

				Drawn	Checked	Approved	SCI BOM No.	1252168	Model Name	Double socket		
				莫罕波	楊金壽	鍾明芳	Customer No.		Model No.	A13-142194BHD-BB3	Rev.	
Date	Name	Description	No.	09/04/25	2025/09/04	2025/09/05	Unit	mm	Shin Chin Industrial Co., Ltd.			0