


TT - Threaded Test Probe

mm [inch]





[0.504]
Installation Height 12.80



TT1000 RA04 N

Minimum centers:	2.54 [.100]
Full travel:	4.40 [.173]
Working travel:	3.50 [.137]
Current rating:	3 - 5 A
Probe resistance:	< 20 mΩ
Operating temperature:	- 40 °C to + 80 °C
Plunger material:	BeCu/ Gold plated
Barrel material:	Brass / Gold plated
Spring material:	Music Wire / Gold plated

Spring force at working stroke: 1.5 N [5.4 oz]

© COPYRIGHT 2023
EQUIP-TEST KFT.
ALL RIGHTS RESERVED

This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!

	Name	Date
Designed	M.K.	2023.09.07
Drawed		
Checked		
Note		

Catalog Item: **TT1000 RA04 N**

Drawing No.:

A4 SHEET 1 OF 1

EQUIP TEST
TEST - SUPPORT - INNOVATE