



EAN-13: 5901969450217
CAT. NO: NFO-2402



SHOBO SH8F ARGB

PC CASE

PRODUCT FEATURES:

- Four efficient Fury Sai S12 ARGB PWM fans with an included controller offer effective cooling and full personalization of lighting effects.
- The refreshed front panel with modern styling provides an attractive look and high airflow for improved cooling.
- The design allows for the installation of AIO radiators in 240/280/360 mm sizes at the front and 240 mm on top of the case.
- The spacious interior allows for the installation of graphics cards up to 330 mm in length and CPU coolers up to 161 mm in height.
- A modern I/O panel with USB 3.0 ports and space for three SSD/HDD drives guarantee extensive system expansion possibilities.

PRODUCT SPECIFICATION:

Type of casing	Midi Tower
Motherboard form factor	ATX, Micro-ATX, Mini-ITX
The maximum length of the PSU	170 mm
Maximum CPU cooling height	161 mm
Maximum length of the GPU graphics card	330 mm
Installed fans	4x 120mm ARGB
Max number of fans	8
Support for installation of fans - top	2x 120 mm, 1x 140 mm
Support for installation of fans - front	3x 120 mm, 3x 140 mm
Support for installation of fans - rear	1x 120 mm
Support for installation of liquid cooling - top	120 mm, 240 mm
Support for installation of liquid cooling - front	120 mm, 140 mm, 280 mm, 360 mm
Support for installation of liquid cooling - rear	120 mm
Number of 2.5" drive bays (SSD/HDD)	2
Number of 3.5" drive bays (SSD/HDD)	2
Material	ABS, Steel, Tempered Glass
Dimensions	336 x 200 x 437 mm

