



## BETA 7247NB BASIC leather safety sandal



### Certifications and Standards



S1P FO SR

EN ISO 20345:2022

### Features

7247NB leather sandals with elastic steel penetration proof insole and steel toe cap for cost-effective protection.

#### FIRST QUALITY PRICE

The perfect balance of durability, functionality and economy. Protection and reliability at your fingertips: safety at work has never been so accessible.

#### STEEL/STEEL PROTECTION

Maximum safety, low cost: our BASICS with steel toe cap and sheet provide reliable and durable protection for all pockets.

#### NEW STANDARD EN ISO 20345:2022

The shoe is S1P FO SR certified according to the latest EN ISO 20345:2022 standard. It is ideal for even the most demanding working environments, thanks to improved slip, oil and penetration resistance.



#### FUNCTIONAL DESIGN

The clean and essential lines are enhanced by bright orange details.



#### LUG OUTSOLE

The anti-static outsole with tread guarantees maximum slip and oil resistance.



#### OPEN UPPER WITH STRAP CLOSURE

The open upper guarantees freshness all day long. Top practicality and comfort thanks to the strap closure.



## Certifications and Standards



## Specifications

LACING:	tear-off
WEIGHT (INDICATIVE SIZE 42):	670 g
TYPE:	low

### Lightness

Leather

### Comfort

Dual-density polyurethane

### Safety



Felt carbon

### Protections

Tip: Steel, 200 joules

Durability: Steel insole

## Coded items

	Art.	EU	UK	 mm
072470635	7247NB 35	35	2,5	228
072470636	7247NB 36	36	3,5	235
072470637	7247NB 37	37	4,5	242
072470638	7247NB 38	38	5	248
072470639	7247NB 39	39	6	255
072470640	7247NB 40	40	6,5	262
072470641	7247NB 41	41	7	268
072470642	7247NB 42	42	8	275
072470643	7247NB 43	43	9	282
072470644	7247NB 44	44	10	288
072470645	7247NB 45	45	10,5	295
072470646	7247NB 46	46	11	302
072470647	7247NB 47	47	12	308
072470648	7247NB 48	48	13	315

Scan the QR Code to access the web tab

Specs, media and documentation in one click.

