

USB Type-C™ Adapter to Gigabit LAN with Power Delivery 100 watt

Description

The adapter by Delock expands a PC or laptop by **one network interface via the USB Type-C™** interface. In addition, the adapter can also be operated on a Thunderbolt™ 3 interface.

USB Power Delivery (USB PD 3.0) support up to 100 watt

The adapter has a USB Type-C™ Power Delivery port to connect the power supply of the laptop or tablet to charge it. The adapter can also be used without a power supply.



Item no. 61026

EAN: 4043619610266

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB 5 Gbps USB Type-C™ male
 - 1 x Gigabit LAN RJ45 jack
 - 1 x USB Type-C™ PD female (power supply)
- Chipset: Realtek RTL8153B, VIA VL102
- SuperSpeed USB - 5 Gbps specification
- Data transfer rate:
 - Ethernet up to 10 Mbps (Half/Full Duplex)
 - Fast Ethernet up to 100 Mbps (Half/Full Duplex)
 - Gigabit Ethernet up to 1000 Mbps (Half/Full Duplex)
- Compatible with:
 - IEEE 802.3: 10BASE-T
 - IEEE 802.3u: 100BASE-TX
 - IEEE 802.3ab: 1000BASE-T
- Supports Auto MDI-X (automatic detection of standard or crossover network cable)
- Supports Wake On LAN (WOL)
- Supports IEEE 802.3az (Energy Efficient Ethernet)
- Supports IEEE 802.1Q Virtual LAN (VLAN)
- Support full duplex operation with IEEE 802.3x flow control and half duplex operation with back-pressure flow control
- Supports 9k Jumbo Frames
- Output power for host: max. 100 W
- LED indicator for power and activity

- USB bus powered
- Colour: black
- Cable length incl. connectors: ca. 17 cm

System requirements

- Android 10.0 or above
- Chrome OS
- Linux Kernel 5.11 or above
- Mac OS 11.5.2 or above
- Windows 8.1/8.1-64/10/10-64/11
- iPad Air (4th Generation) or above
- iPad Pro (3rd Generation) or above
- Surface Pro 7
- Device with a free USB Type-C™ port or with a free Thunderbolt™ 3 port

Package content

- USB Type-C™ Gigabit LAN adapter
- User manual

Images



General

Supported operating system:	Chrome OS Windows 10 32-Bit Windows 10 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit Android 10.0 or above iPad Pro (3rd Generation) or above iPad Air (4th Generation) or above Windows 11 Linux Kernel 5.11 or above Mac OS 11.5.2 or above
LED indicator:	2 x

Interface

Connector 1:	1 x USB 5 Gbps USB Type-C™ male
Connector 2:	1 x Gigabit LAN RJ45 jack
Connector 3:	1 x USB Type-C™ Power Delivery female

Technical characteristics

Chipset:	Realtek RTL8153B VIA VL102
Data transfer rate:	Ethernet up to 10 Mbps Fast Ethernet up to 100 Mbps Gigabit Ethernet up to 1000 Mbps

Physical characteristics

Colour:	black
---------	-------

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de

Website www.delock.de