

BW 861MIX/C62 Set of 60 bits and 2 accessories, in pocket-size case



- 1/4" hexagon drive
- For manual, electric and pneumatic drivers
- Bits □ 25mm LP: 3-4(x2)-4,5-5(x2)-5,5-6(x2)-7mm
- Bits □ 25mm PH: PH0(x2)-PH1(x2)-PH2(x2)-PH3(x2)
- Bits □ 25mm PZ: PZ0(x2)-PZ1(x2)-PZ2(x2)-PZ3(x2)
- Bits □ 25mm TX: T10(x2)-T15(x2)-T20(x2)-T25(x2)-T27-T30
- Bits □ 25mm PE: 2-3-4-5-6mm
- Bits □ 25mm SQ: 0-1-2-3
- Bits □ 50mm LP: 5-6mm
- Bits □ 50mm PH: PH1-PH2
- Bits □ 75mm LP: 5mm
- Bits □ 75mm PH: PH1
- Bits □ 75mm TX: T10-T15
- Bits □ F: 5-6-7-8-3-10-11mm
- Bit holder: □ - □

	Art.
008616962	BW 861MIX/C62



Scan the QR Code to access the web tab
Specs, media and documentation in one click.





BETA BW 2002/B20

Fabric roll-up bag with assortment of 20 tools



Features

BW 2002/B20 the roll-up envelope for every situation

COMPACT

Compact and light, weighing just over a kilo: a kit designed to be always ready for use and suitable for every situation, from professional work to emergencies.

ORGANISATION

Maximum organisation with 12 dedicated compartments: every tool is always in its place, clearly visible and ready to use, for quick, tidy and efficient work

BW 96/SC9: n. 9 Set of 9 offset hexagon key wrenches □ 1,5-2-2,5-3-4-5-6-8-10 mm
BW 1128BMX: n. 1 Electrician's scissors, stainless steel blades, with microteeth
BW 1150BM 180: n. 1 Heavy-duty combination pliers □ 180 mm
1201E: n. 1 0,8x4x100 mm
1202E: n. 2 PH1x80 - PH2x100 mm

Coded items

	Art.
020026920	BW 2002/B20



1692

Measuring tapes, shock-resistant bi-material ABS casings, steel tapes, precision class II

CE

	art.	L m	S mm			 g
016920052	1692/2	2	16			90
016920053	1692/3	3	16			110
016920055	1692/5	5	19			200
016920058	1692/8	8	25			380





Scheda tecnica

No.11FA01B

VersioneV01.1

Famiglia prodotto:

Fascette - Fascette in nylon UV resistant

Codici articolo:

N0824, N0824M, N1025, N1025M, N1225, N1625, N1625M, N2025, N1436, N1436M, N2036, N2936, N2936M, N3736, N1248, N1648, N1948, N2048, N2048M, N2548, N3048, N3048M, N3748, N3948, N4348, N5348, N1576, N2076, N2976, N3776, N4576, N5476, N7576, N4390, N5390, N7190, N7890, N8190, N1090, N1290, N1590

Descrizione:

FASCETTE IN NYLON RESISTENTI AI RAGGI UV - STANDARD

Immagine



Specifiche

MATERIALE:

poliammide (PA 6.6) + carbon black

COLORE:

nero

LIVELLO AUTOESTINGUENZA:

UL 94 V2

TEMPERATURA ESERCIZIO:

da -40 °C a +85 °C

TEMPERATURA MIN. INSTALLAZIONE:

-10 °C

RESISTENZA AGLI AGENTI CHIMICI:

buona resistenza alle basi, agli olii, ai grassi, ai solventi di cloruro. Limitata resistenza agli acidi. Non resistente ai fenoli.

NORME DI RIF.:

EN 62275:2015-02

CLASSIFICAZIONE:

tipo 1 (EN), tipo 21 (UL)

MONTAGGIO:

aprire la confezione poco prima dell'utilizzo

Codice	Larghezza (mm)	Lunghezza (mm)	Ø max di serraggio (mm)	Ø min di serraggio (mm)	Resistenza minima di trazione (N)	
N0824	2,5	80	14	3	80	100/8000
N0824M	2,5	80	14	3	80	1000/8000
N1025	2,5	100	20,5	3	80	100/5000
N1025M	2,5	100	20,5	3	80	1000/5000
N1225	2,5	120	27	3	80	100/5000
N1625	2,5	160	40	3	80	100/4000
N1625M	2,5	160	40	3	80	1000/4000
N2025	2,5	200	52,5	3	80	100/3000
N1436	3,6	140	33	3	180	100/2500
N1436M	3,6	140	33	3	180	1000/2500
N2036	3,6	200	52,5	3	180	100/2000
N2936	3,6	300	106	3	180	100/1500
N2936M	3,6	300	106	3	180	1000/1500
N3736	3,6	370	105	3	180	100/4000
N1248	4,6	120	24	3	220	100/2000
N1648	4,6	160	36	3	220	
N1948	4,8	188	46	3	220	100/1500
N2048	4,8	200	50	3	220	
N2048M	4,8	200	50	3	220	1000/1500
N2548	4,8	250	65	3	220	100/1300
N3048	4,8	300	81	3	220	100/1000
N3048M	4,8	300	81	3	220	1000/1000
N3748	4,8	370	103,5	3	220	100/3000
N3948	4,8	390	110	3	220	100/2500
N4348	4,8	430	122,5	3	220	100/1500
N5348	4,8	530	160	3	220	100/100
N1576	7,6	150	24	6	550	100/1000
N2076	7,6	200	51	6	550	100/800
N2976	7,6	300	83	6	550	100/600
N3776	7,6	370	103,5	6	550	100/1000
N4576	7,6	450	130,5	6	550	
N5476	7,6	540	159	6	550	100/100
N7576	7,6	750	226	6	550	
N4390	9	430	130,5	9	800	
N5390	8,8	550	163,5	9	800	
N7190	8,8	710	195	9	800	
N7890	8,8	780	235,5	9	800	
N8190	9	810	245	9	800	100/100
N1090	9	1020	295	9	800	
N1290	9	1220	375,5	9	800	
N1590	9	1530	460	9	800	



file n° E 223175

HALOGEN

FREE



UV
RESISTANT

BM SPA - Viale Milano 54/56 - 20089 Rozzano (MI) Italy



Technical sheet

No.78NA01A

IssueV01.0

Product family:

Electrical tapes - PVC electrical tape

Item code:

ESB1510BI, ESB1510BL, ESB1510GI, ESB1510GR, ESB1510GV, ESB1510MA, ESB1510NE, ESB1510RO, ESB1510VE, ESB1525BI, ESB1525BL, ESB1525GI, ESB1525GR, ESB1525GV, ESB1525MA, ESB1525NE, ESB1525RO, ESB1525VE, ESB1925BI, ESB1925BL, ESB1925GI, ESB1925GR, ESB1925GV, ESB1925MA, ESB1925NE, ESB1925RO, ESB1925VE, ESB2525BI, ESB2525BL, ESB2525GI, ESB2525GR, ESB2525GV, ESB2525MA, ESB2525NE, ESB2525RO, ESB2525VE

Description:

ELECTRICAL TAPE · PVC · 0.15 THICKNESS

Image



Specifications

MATERIAL:

PVC

RESISTANT TO:

acids, weathering, corrosion, alkalis, oil, humidity

OPERATING TEMPERATURE:

0°C - +90°C

TENSILE STRENGTH:

28 N/cm equivalent to 18.6 N/mm²

ELONGATION:

200

ADHESION TO STEEL:

2.2

ADHESION TO BACKING:

2

DIELECTRIC STRENGTH:

45

DIELECTRIC STRENGTH:

45 kV/mm

ACCORDING TO STD.:

IEC 60454-2

FLAMMABILITY:

flame retardant

CLASSIFICATION:

EN 60454-3-1-5/F-PVCP/90

ACCORDING TO STD.:

IEC 60454-2

Code	Color	Thickness (mm)	Height (mm)	Length (m)	
ESB1510BI	 White	0,15	15	10	10/200
ESB1510BL	 Blue	0,15	15	10	
ESB1510GI	 Yellow	0,15	15	10	
ESB1510GR	 Grey	0,15	15	10	
ESB1510GV	 YellowGreen	0,15	15	10	
ESB1510MA	 Brown	0,15	15	10	
ESB1510NE	 Black	0,15	15	10	
ESB1510RO	 Red	0,15	15	10	
ESB1510VE	 Green	0,15	15	10	
ESB1525BI	 White	0,15	15	25	10/100
ESB1525BL	 Blue	0,15	15	25	
ESB1525GI	 Yellow	0,15	15	25	
ESB1525GR	 Grey	0,15	15	25	
ESB1525GV	 YellowGreen	0,15	15	25	
ESB1525MA	 Brown	0,15	15	25	
ESB1525NE	 Black	0,15	15	25	
ESB1525RO	 Red	0,15	15	25	
ESB1525VE	 Green	0,15	15	25	
ESB1925BI	 White	0,15	19	25	10/100
ESB1925BL	 Blue	0,15	19	25	
ESB1925GI	 Yellow	0,15	19	25	
ESB1925GR	 Grey	0,15	19	25	
ESB1925GV	 YellowGreen	0,15	19	25	
ESB1925MA	 Brown	0,15	19	25	
ESB1925NE	 Black	0,15	19	25	
ESB1925RO	 Red	0,15	19	25	
ESB1925VE	 Green	0,15	19	25	
ESB2525BI	 White	0,15	25	25	8/80
ESB2525BL	 Blue	0,15	25	25	
ESB2525GI	 Yellow	0,15	25	25	
ESB2525GR	 Grey	0,15	25	25	
ESB2525GV	 YellowGreen	0,15	25	25	
ESB2525MA	 Brown	0,15	25	25	
ESB2525NE	 Black	0,15	25	25	
ESB2525RO	 Red	0,15	25	25	
ESB2525VE	 Green	0,15	25	25	



FLAME

RETARDANT

BM SPA - Viale Milano 54/56 - 20089 Rozzano (MI) Italy