

USB 2.0 Card Reader USB Type-C™ male 5 Slots

Description

The card reader by Delock can be used for reading and writing memory cards and can be connected to the USB-C™ interface of e.g. PCs, laptops, MacBooks, Chromebooks or smartphones.



Item no. 91739

EAN: 4043619917396

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB Type-C™ 2.0 male >
 - 1 x SD / MMC slot
 - 1 x Micro SD slot
 - 1 x xD slot
 - 1 x MS slot
 - 1 x CF slot
- Chipset: MA8168
- Supports memory: up to 2 TB SD 3.0 (UHS-I), MS
- Data transfer rate up to 480 Mbps
- LED indicator blue for read and write process
- Android devices: data medium can only be used in FAT32 and exFAT format
- It can only be used one storage medium, not several at the same time
- No external power supply needed
- Plug & Play
- Dimensions (LxWxH): ca. 101.5 x 27 x 15 mm
- Cable length incl. connector: ca. 15 cm
- Colour: black

- Supports following memory cards:
 - Slot 1 Secure Digital / Multi Media Card**
 - SD, SDHC, SDXC, Extreme SD, Extreme II SD, Extreme III SD, Ultra SD, Ultra II SD, Ultra II SD P Plus, SD Ultra-X, Ultra Speed SD, SD Pro, SD Elite Pro, HS SD, MMC, MMC 4.0

Slot 2 Micro SD

Micro SD, Micro SDHC, Micro SDXC

Slot 3 xD

xD, xD 1.21

Slot 4 MS

MS, MS Pro Duo, MS MG Pro, MS MG Pro Duo, HS MS MG Pro Duo, HS MS Pro Duo

Slot 5 CF

CF I, CF II, CF 3.0, CF 4.0, Extreme III CF, Extreme CF, Ultra II CF, HS CF, XS-XS CF, CF Elite Pro, CF Pro, CF Pro II

System requirements

- Android 6.0 or above
- Mac OS 10.12 or above
- Windows 7/7-64/8.1/8.1-64/10/10-64/11
- Device with a free USB Type-C™ port

Package content

- Card reader
- User manual

Images



General

Function:	Plug & Play
Supported operating system:	Android 6.0 or above Mac OS 10.12 or above Windows 10 32-Bit Windows 10 64-Bit Windows 7 32-Bit Windows 7 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit Windows 11

Supported memory card:

- Micro SD
- Micro SDHC
- Micro SDXC
- SD
- Extreme SD
- SDHC
- SDXC
- CF I
- CF II
- MMC
- MS
- MS PRO Duo
- MMC 4.0
- Extreme II SD
- Extreme III SD
- Ultra SD
- Ultra II SD
- Ultra II SD P Plus
- SD Ultra-X
- Ultra Speed SD
- SD Pro
- SD Elite Pro
- HS SD
- xD
- xD 1.21
- MS MG Pro
- MS MG Pro Duo
- HS MS MG Pro Duo
- HS MS Pro Duo
- CF 3.0
- CF 4.0
- Extreme III CF
- Extreme CF
- Ultra II CF
- HS CF
- XS-XS CF
- CF Elite Pro
- CF Pro
- CF Pro II

Interface

Output:	1 x CF slot 1 x xD slot 1 x Micro SD Slot 1 x SD / MMC slot 1 x MS slot
Input:	1 x USB Type-C™ male

Technical characteristics

Chipset:	Prolific MA8168
Data transfer rate:	480 Mbps

Physical characteristics

Cable length incl. connectors:	15 cm
Length:	101.5 mm
Width:	27.0 mm
Height:	15 mm
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de