



BETA 7243NFT BASIC leather occupational shoe, water-repellent



Certifications and Standards



O2 FO SR RS

EN ISO 20347:2011

Features

The 7243NFT smooth water-repellent leather shoe with a two-density polyurethane outsole for cost-effective protection.

FIRST QUALITY PRICE

The perfect balance of durability, functionality and economy. Protection and reliability at your fingertips: safety at work has never been so accessible.

WATERPROOF

The high-quality smooth leather upper is perfect for protection in all weather conditions thanks to its water-repellent properties.

NEW EN ISO 20347:2022 STANDARD

The shoe is O2 FO SR certified according to the latest EN ISO 20347:2022 standard. It is ideal for less demanding work environments, thanks to improved slip and oil resistance.



FUNCTIONAL DESIGN

The clean and essential lines are enhanced by bright orange details.



LUG OUTSOLE

The anti-static outsole with tread guarantees maximum slip and oil resistance.



PROTECTIVE GUSSET AND QUICK RELEASE

Leather gusseted tongue protects against annoying seepage of liquids and debris. Top safety thanks to quick release.



Certifications and Standards



Specifications

LACING:	traditional
WEIGHT (INDICATIVE SIZE 42):	615 g
TYPE:	high

Lightness

Water-repellent leather

Comfort

Dual-density polyurethane

Safety



Felt carbon

Protections

Tip: Not available

Durability: Not available

Coded items

	Art.	EU	UK	 mm
072430535	7243NFT 35	35	2,5	228
072430536	7243NFT 36	36	3,5	235
072430537	7243NFT 37	37	4,5	242
072430538	7243NFT 38	38	5	248
072430539	7243NFT 39	39	6	255
072430540	7243NFT 40	40	6,5	262
072430541	7243NFT 41	41	7	268
072430542	7243NFT 42	42	8	275
072430543	7243NFT 43	43	9	282
072430544	7243NFT 44	44	10	288
072430545	7243NFT 45	45	10,5	295
072430546	7243NFT 46	46	11	302
072430547	7243NFT 47	47	12	308
072430548	7243NFT 48	48	13	315

Scan the QR Code to access the web tab

Specs, media and documentation in one click.

