



2470E

Product no.: 2470E


Tip cutter - straight long relieved head



This head is suitable for horizontal and vertical cuts.






The long tips facilitate cutting in hard-to-reach areas.



source images

The Perfect Cut - Strong, sharp and precise, every time

The Weller Erem Series 2400 Magic Sense is a range of medium-sized precision cutters that combines robustness, visibility and accessibility. A large variety of head shapes for precision work in hard-to-reach areas. The optimized ergonomic shape of the Series 2400 MagicSense prevents hand fatigue. These cutters are manufactured from improved induction-hardened cutting edges up to 64 – 65 HRC for an extremely long service life. The cutting edges are made from special tool steel. The precision cutters have a nonreflecting surface, are ESD safe and resharpenable.

Type			Type of Cut	Cutting Capacity																							
Series 2400 MagicSense				mm	0,03	0,1	0,2	0,3	0,4	0,5	0,6	0,7	0,8	0,9	1,0	1,1	1,2	1,3	1,4	1,5	1,6	1,7	1,8	1,9	2,0		
				Inch	.0001	.003	.007	.011	.015	.019	.023	.027	.031	.035	.039	.043	.047	.051	.055	.059	.062	.066	.070	.074	.078		
	2412E		Semi Flush																								
	2422E		Flush																								
	2432E		Super Full Flush																								
	2477E		Flush																								
	2403E		Flush																								
	2404E		Flush																								
	2482E		Flush																								
	2475E		Flush																								
	2470E		Flush																								
	2476TX2		Flush / Carbide																								





Technical Data

Length mm	140
Length of cutting edges mm	5
Head width mm	11
Head thickness mm	6
Head length mm	30
Max. cutting capability – hard wire mm	---
Weight in oz	2.698
Length of cutting edges Inches	0.157
Head width Inches	0.433
Head thickness Inches	0.236
Head length Inches	1.181
ESD-safe	on
Cut	Flush
Max. cutting capability – medium hardness mm	Ø 0,4
Max. cutting capability – copper wire mm	Ø 0,6
Length inches	5.512
Weight in g	76.5
Erem applications	---