

mm [inch]





ST1000 SG54 N

Minimum centers:	2.54 [.100]
Full travel:	6.35 [.250]
Working travel:	4.00 [.157]
Current rating:	5 - 8 A
Probe resistance:	< 20mΩ
Operating temperature:	-40°C up to +150°C
Plunger material:	Steel / Gold plated
Barrel material:	PhBr / Gold plated
Spring material:	Stainless steel / Gold plated

Spring force at working stroke: 2.0 N [7.2 oz]

© COPYRIGHT 2022
EQUIP-TEST KFT.
ALL RIGHTS RESERVED

This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!

	Name	Date
Designed	M.K.	2022.08.15
Drawed		
Checked		
Note		

Catalog Item: **ST1000 SG54 N**

Drawing No.:

A4 | SHEET 1 OF 1

EQUIP TEST
TEST – SUPPORT – INNOVATE