



Antenna Cable RP-SMA jack bulkhead to I-PEX Inc., MHF® 4L LK plug 1.37 10 cm thread length 10 mm splash proof

Description

The antenna cable by Delock is suitable for connecting components of radio frequency technology.

This cable is suitable for applications with high shock and vibration environment due to its internal locking.



Item no. 12655

EAN: 4043619126552

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x RP-SMA jack bulkhead >
 - 1 x I-PEX Inc., MHF® 4L LK plug
- Thread length: 10 mm
- Impedance: 50 Ohm
- Cable: coaxial
- Cable type: 1.37
- Cable attenuation: 2.5 dB @ 2.4 GHz per meter
- Cable diameter: ca. 1.37 mm
- Smallest bending radius: 4.5 mm
- Length incl. connectors: ca. 10 cm

System requirements

- Device with one free RP-SMA or I-PEX Inc., MHF® I port

Package content

- Antenna cable

General

Protection class:	Splash proof
-------------------	--------------

Interface

Connector 1:	1 x RP-SMA jack bulkhead
Connector 2:	1 x I-PEX Inc., MHF® 4L LK plug

Technical characteristics

Impedance:	50 Ω
------------	------

Physical characteristics

Thread length:	10 mm
Cable category:	coaxial
Cable type:	1.37
Cable attenuation:	2.5 dB @ 2.4 GHz per meter
Cable colour:	grey black
Cable length incl. connectors:	10 cm
Smallest bending radius:	9 mm
Cable diameter:	1.37 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

