



BETA 7271V FitEVOLUTION suede shoe, perforated



Certifications and Standards

CE S1PS FO SR ESD EN ISO 20345:2022

Features

Model 7271V is the perfect synthesis of softness and functionality: the outsole and neon green details enhance the comfort of the suede upper.

FIT4YOU system

Create your own comfort with BETA's patented FIT4YOU system: a special cavity in the penetration proof insole allows you to replace the ETPU insole at any time, choosing from three different densities included in the pack.

ETPU inserts

ETPU is known for its excellent anti-shock and shock-absorbing properties. The three inserts soft, intermediate and rigid make it easy and immediate to customise the softness and support of the shoe to suit your needs.

Soft and resistant

The suede upper is incredibly soft and comfortable, perfect for all-season use. It is also surprisingly durable, ideal for shoes built to last, without compromising on quality.

Metal-free

Composite toe cap and midsole are made of composite material to provide lightweight, metal-free protection.



FIT4YOU
The patented FIT4YOU technology, with the 3 ETPU inserts included in the pack, allows the shoe's cushioning to be customised.



Customised comfort
The special pressed sheet allows you to create your own comfort by choosing from 3 different ETPU inserts included in the pack.



ESD protection
ESD certified to protect user and machinery from electrostatic charges.



Certifications and Standards

CE S1PS FO SR ESD EN ISO 20345:2022



Specifications

LACING: traditional
 WEIGHT (INDICATIVE SIZE 42): 550 g
 TYPE: low

Lightness

- Perforated suede
- Heel stability support
- Traditional lacing

Comfort

Dual-density polyurethane

Safety

3-density cushioning ETPU insert and EVA FOAM underfoot cover

Protections

Tip: Polymer material, 200 joules.

Durability: Composite fibre, ceramic treatment.

Coded items

	Art.	EU	UK	 mm
072710137	7271V 37	37	4,5	251
072710138	7271V 38	38	5	257
072710139	7271V 39	39	6	263
072710140	7271V 40	40	6,5	269
072710141	7271V 41	41	7	276
072710142	7271V 42	42	8	282
072710143	7271V 43	43	9	290
072710144	7271V 44	44	10	296
072710145	7271V 45	45	10,5	304
072710146	7271V 46	46	11	311
072710147	7271V 47	47	12	317
072710148	7271V 48	48	13	324

Scan the QR Code to access the web tab

Specs, media and documentation in one click.

