

Professional grade SD card

SDXC

goodram
PRO



Main Features

- UHS-II U3 interface
- Available capacities: 128 GB
- Up to 265 MB/s read speed
- V60 Video Speed Class
- Perfect for 4K video processing
- Extremal durability
- Lifetime warranty



GOODRAM PRO UHS-II U3 microCARD delivers high performance and reliability for users who want to record 4K and slow-motion videos or capture high-quality photos in JPEG and RAW formats, even in fast-response shooting modes.

Parameters

Available capacities	128 GB
Card standard	SDXC
Max. transfer	read: up to 265 MB/s write: up to 120 MB/s
Card dimensions	24.0 x 32.0 x 2.1 [mm]
Interface speed	UHS-II U3
Video Class Standard	V60
Blister dimentions	103 x 123 [mm]
Operating temperature	-25 do +85°C
Storage temperature	-40°C ~ 85°C

Details

PRODUCT	CAPACITY	P/N	EAN
GOODRAM PRO S6B0	128 GB	GPSD6B0-1280RX1	5908267915042

¹ Based on internal tests using PCI-e adapter. Speed may vary depending on the testing methodology and platform and operating system.
² Card operation and performance will vary based on host device.

Professional grade SD card

SDXC



Logistic data

P/N	EAN	MOQ	PRODUCT DIMENSIONS (mm)	PRODUCT WEIGHT (g)	BLISTER DIMENSIONS (mm)	PRODUCT WEIGHT IN BLISTER (g)	MOQ CARTON DIMENSIONS (mm)	MOQ CARTON WEIGHT (g)	COLLECTIVE PACKAGING DIMENSIONS (mm)	COLLECTIVE PACKAGING WEIGHT (kg)
GPSD6B0-1280RX1	5908267915042	10	24×32×2.1	2	60 × 100 × 9.5	13	131 × 88 × 72	165	515 × 280 × 125	2.5

¹ Based on internal tests using PCI-e adapter. Speed may vary depending on the testing methodology and platform and operating system.
² Card operation and performance will vary based on host device.