

# USB Type-C™ Docking Station with M.2 Slot - 4K HDMI / USB / LAN / PD 3.0

## Description

This docking station by Delock can be connected to a computer with a USB-C™ DP Alt Mode or Thunderbolt™ 3 port and provides a variety of interfaces. A monitor can be operated at the **HDMI output**. **Two built-in USB 3.2 Gen 1** ports allow the use of peripherals and a connector for **gigabit network** completes the features.

### Slot for M.2 SSD with key B

On the bottom is an **M.2 slot**. An M.2 SATA SSD in 2280, 2260, 2242 or 2230 format can be connected to this slot.

### USB Power Delivery (USB PD 3.0) support up to 100 watt

The docking station has a USB Type-C™ Power Delivery port to connect the power supply of the laptop or tablet to charge it. The docking station can also be used without a power supply.

### Small sturdy helper

Due to its **small dimensions and its sturdy housing**, this Delock docking station is particularly suitable for travelling. It can simply be packed into the bag together with the laptop or tablet and used as needed.



**Item no. 87767**

EAN: 4043619877676

Country of origin: China

Package: Retail Box

## Technical details

- Connectors:
  - 1 x USB Type-C™ male
  - 2 x SuperSpeed USB (USB 3.2 Gen 1) Type-A female
  - 1 x HDMI-A female
  - 1 x Gigabit LAN 10/100/1000 Mbps RJ45 jack
  - 1 x USB Type-C™ female (power supply)
  - 1 x 67 pin M.2 key B slot
- Resolution up to 3840 x 2160 @ 30 Hz (depending on the system and the connected hardware)
- Transmission of audio and video signals
- Supports HDCP 1.4 and 2.2
- Input power: 1 x USB Type-C™ female max. 100 W
- Supports M.2 modules in format 2280, 2260, 2242 and 2230 with key B or key B+M

- based on SATA
- Metal housing
- LED indicator for power and access
- Cable length without connector: ca. 18 cm
- Colour: grey
- Dimensions (LxWxH): ca. 123 x 50 x 14 mm

---

## System requirements

- Android 9.0 or above
- Chrome OS 78.0 or above
- iPad Pro (3rd Generation) or above
- Linux Kernel 4.6.4 or above
- Mac OS 10.15.3 or above
- Windows 8.1/8.1-64/10/10-64
- Device with a free USB Type-C™ port and DisplayPort alternate mode or with a free Thunderbolt™ 3 port

---

## Package content

- USB-C™ docking station
- User manual

---

## Images



## General

Supported operating system:	Android 9.0 or above Chrome OS 78.0 or above Linux Kernel 4.6.4 or above Mac OS 10.15.3 or above Windows 10 32-Bit Windows 10 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit iPad Pro (2018)
Supported module:	M.2 modules in format 2280, 2260, 2242 and 2230 with key B or key B+M based on SATA

## Interface

Connector 1:	1 x USB Type-C™ male
Connector 2:	2 x USB 5 Gbps Type-A female
Connector 3:	1 x HDMI-A female
Connector 4:	1 x Gigabit LAN RJ45 jack
Input:	1 x USB Type-C™ female (power supply)
Internal:	1 x 67 pin M.2 key B slot

## Technical characteristics

Maximum screen resolution:	3840 x 2160 @ 30 Hz
----------------------------	---------------------

## Physical characteristics

Length:	123 mm
Width:	50 mm
Height:	14 mm
Colour:	grey

## Manufacturer information

Street Beeskowdamm 13/15

Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de