

# USB 40 Gbps USB Type-C™ Network Adapter 10 Gigabit LAN 1 x RJ45

## High speed: Data transfer rates up to 10 Gbps

This USB network adapter by Delock offers a reliable and fast network connection. With a transmission speed of up to 10 gigabits per second, it enables efficient working and smooth streaming.

## NBASE-T for higher speed

Modern services and new technologies require higher bandwidths. NBASE-T technology enables speeds of 1 Gbps, 2,5 Gbps and 5 Gbps with conventional networking cables. The best possible transmission rate is set automatically.

## Thunderbolt™ 3, Thunderbolt™ 4 or USB-C™ 40 Gbps

The adapter can be connected to a PC or laptop via Thunderbolt™ 3, Thunderbolt™ 4 or USB-C™ 40 Gbps interface. Operation on slower USB ports is not possible.



**Item no. 64349**

EAN: 4043619643493

Country of origin: China

Package: White Box

## Technical details

- Connectors:
  - 1 x USB 40 Gbps USB Type-C™ male
  - 1 x 10 Gigabit LAN RJ45 jack
- Chipset: Aquantia AQC113CS, Asmedia ASM2464PDX
- Data transfer rate:
  - Ethernet up to 10 Mbps
  - Fast Ethernet up to 100 Mbps
  - Gigabit Ethernet up to 1 Gbps
  - NBASE-T with up to 2.5 Gbps and 5 Gbps
  - 10 Gigabit Ethernet up to 10 Gbps
- Supports IEEE 802.3az (Energy Efficient Ethernet)
- Supports 16k Jumbo Frames
- Supports IEEE 802.1Q Virtual LAN (VLAN)
- Supports Wake On LAN (WOL)
- LED indicator for link and activity
- USB bus powered
- Robust aluminum housing
- Fanless
- Colour: silver
- Dimensions (LxWxH): ca. 111 x 55 x 25 mm

---

## System requirements

- Linux Kernel 6.5 or above
- Mac OS 14.5 or above
- Windows 11
- PC or laptop with a free USB Type-C™ 40 Gbps or Thunderbolt™ 3/4 port

---

## Package content

- USB Type-C™ 10 Gigabit LAN adapter
- USB Type-C™ to USB Type-C™ cable, length ca. 30 cm
- User manual

---

## Images



## General

Supported operating system:	Windows 11 Linux Kernel 6.5 or above Mac OS 14.5 or above
LED indicator:	Link and activity

## Interface

Connector 1:	1 x USB 40 Gbps USB Type-C™ male
Connector 2:	1 x Gigabit LAN RJ45 jack

## Technical characteristics

Chipset:	Aquantia AQC113CS Asmedia ASM2464PD
Data transfer rate:	Ethernet up to 10 Mbps Fast Ethernet up to 100 Mbps Gigabit Ethernet up to 1 Gbps Gigabit Ethernet up to 10 Gbps Gigabit Ethernet up to 2.5 Gbps Gigabit Ethernet up to 5 Gbps

## Physical characteristics

Housing material:	Aluminium
Cable length:	30 cm
Length:	111 mm
Width:	55 mm
Height:	25 mm
Colour:	anthracite

## Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland

E-Mail	<a href="mailto:info@delock.de">info@delock.de</a>
Website	<a href="http://www.delock.de">www.delock.de</a>