

Antenna Cable N plug > SMA plug Twin Cable RG-58 C/U 10 m

Description

This twin cable is particularly suitable for antennas with two connectors, so two individual cables are not required.



Item no. 89468

EAN: 4043619894680

Country of origin: Taiwan,
Republic of China

Package: Zip poly bag

Technical details

- Connectors:
 - 2 x N plug >
 - 2 x SMA plug
- Impedance: 50 Ohm
- Cable: coaxial
- Cable type: RG-58 C/U
- Cable attenuation: 0.73 dB @ 1.0 GHz per meter
- Cable diameter: ca. 2 x 4.95 mm
- Smallest bending radius: 20 mm
- Cable colour: black
- Length incl. connectors: ca. 10 m

System requirements

- Device with N or SMA jack

Package content

- Antenna cable

Images



Interface

Connector 1:	2 x N plug
Connector 2:	2 x SMA plug

Technical characteristics

Impedance:	50 Ω
------------	-------------

Physical characteristics

Cable category:	coaxial
Cable type:	RG-58 C/U
Cable attenuation:	0.73 dB @ 1.0 GHz per meter
Cable colour:	black
Cable length incl. connectors:	10 m
Smallest bending radius:	20 mm
Cable diameter:	2 x 4.95 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

