

mm [inch]





SPT1600 FD12 LX

Minimum centers:	4.00[.157]
Full travel:	5.50[.216]
Working travel:	4.40[.173]
Current rating:	5 - 8 A
Probe resistance:	< 30 mΩ
Operating temperature:	-30°C up to +120°C
Plunger material:	BeCu / Gold plated
Barrel material:	Brass / Gold plated
Spring material:	Steel / Gold plated

Spring force at working stroke: 3.0 N [10.8 oz]

© COPYRIGHT 2022
EQUIP-TEST KFT.
ALL RIGHTS RESERVED

This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!

	Name	Date
Designed	M.K.	2022.10.28
Drawed		
Checked		
Note		

Catalog Item: **SPT1600 FD12 LX**

Drawing No.:

A4 | SHEET 1 OF 1

EQUIP TEST
TEST – SUPPORT – INNOVATE