

Media Converter 1000Base-X SFP to SFP

Opis

This Gigabit Ethernet Media Converter by Delock can be used to connect different optical media. For example, multimode fiber can be converted to singlemode fiber. In the SFP slots, various optional 1 Gb/s SFP modules by Delock can be used.



Numer artykułu 86203

EAN: 4043619862030

Kraj pochodzenia: China

Opakowanie: White Box

Szczegóły techniczne

- Connector:
2 x SFP slot for 1000Base-X SFP module (SFP modules not included)
- Data transfer rate up to 1 Gb/s
- 6 LEDs for status monitoring
- Power consumption: 2.5 W
- Operating temperature: 0° ~ 55° C
- Metal housing
- Fanless
- Dimensions (LxWxH): ca. 95 x 70 x 26 mm

Specyfikacje źródła zasilania

- Power supply type: Euro wall power plug
- Model identifier: KA0601A-0501000EU
- Input voltage: 100 - 240 V
- Input AC frequency: 50 / 60 Hz
- Input current: 0.2 A
- Output voltage / Output current / Output power: 5.0 V / 1.0 A / 5.0 W
- Average active efficiency: 75.5 %
- No-load power consumption: 0.09 W
- DC power connector: 5.5 x 2.1 mm
- Ground outside, plus inside

Wymagania systemowe

- 1000Base-X SFP module

Zawartość opakowania

- Media Converter
- Power supply
- User manual

Zdjęcia



Interfejs

Wyjście:	1 x SFP żeńskie
Wejście:	1 x SFP żeńskie 1 x 5 V DC female 5,5 mm x 2,1 mm

Właściwości techniczne

Szybkość transmisji danych:	Gigabit Ethernet up to 1 Gbps
-----------------------------	-------------------------------

Właściwości fizyczne

Obudowa kolor:	czarny
Materiał obudowy:	metal
Długość:	95 mm
Szerokość:	70 mm
Wysokość:	26 mm

Zasilacz

Typ zasilania:	Euro wall power supply
Napięcie wejściowe:	AC 100 - 240 V / 50 - 60 Hz / 0,2 A
Wyjście zasilania:	5,0 V / 1,0 A
Złącze zasilania:	DC male 5.5 mm x 2.1 mm

Manufacturer information

Ulica	Beeskowdamm 13/15
Kod pocztowy	14167
Miasto	Berlin
Kraj	Deutschland
Email	info@delock.de
Strona internetowa	www.delock.de

