


DIN 5234

	art.	L mm	Ø max "	Ø max mm	A mm	S mm	W g
003780025	378 250	250	1/2" gas	21	17	9	490
003780032	378 320	320	1" gas	34	19	12	792
003780041	378 410	410	1 1/2" gas	49	22	14	1400
003780055	378 550	550	2" gas	60	26	15	2436
003780065	378 650	650	3" gas	90	36	18	4287

