

RJ45 Network Cable Cat.8.1 F/FTP Slim 0.3 m blue

Description

This network cable by Delock can be used to connect various devices and is suitable for 40GBASE-T Ethernet applications with a frequency of 2 GHz and a data transfer rate of up to 40 Gbps.

Slim patch cable

The thin patch cables are characterised by their small cable diameter and enable flexible and space-saving cabling in the network cabinet.



Item no. 80331

EAN: 4043619803316

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x RJ45 plug
 - 1 x RJ45 plug
- Cat.8.1 specification
- Data transfer rate up to 40 Gbps
- Bandwidth: 2000 MHz
- Shielded (F/FTP)
- Slim
- Cable gauge: 28 AWG
- Cable diameter: ca. 4.9 mm
- Cable jacket material: LSZH
- Colour: blue
- Length: ca. 0.3 m

System requirements

- A free RJ45 jack

Package content

- RJ45 cable

Images



General

Specification:	Cat. 8.1
Style:	both sides identical

Interface

Connector 1:	1 x RJ45 male
Connector 2:	1 x RJ45 male

Technical characteristics

Data transfer rate:	Gigabit Ethernet up to 40 Gbps
---------------------	--------------------------------

Physical characteristics

Cable gauge:	28 AWG
Material:	LSZH (halogen-free)
Length:	0.3 m
Colour:	blue
Cable diameter:	4.9 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de