



## BETA 1227TX

### Morphos screwdrivers for Torx® head screws, with handles



### Certifications and Standards



## Features

Designed to reduce fatigue and ensure high torque transmission even in the most demanding applications.

### HIGH TORQUE TRANSMISSION

The innovative tri-material handles with a rigid polypropylene core and double soft bits ensure effective and constant force transmission. Controlled deformation zones adapt to the palm contact points, improving thrust and clamping efficiency.

### CONTROL AND PRECISION

The ergonomic shape and designed index finger and thumb rests guarantee a firm grip and precise centring of the blade on the screw. Even with dirty hands or gloves, you achieve maximum directionality and safety during use.

### PERFECT GRIP AND ANTI-ROLL

The embossed texture ensures a reliable grip even under the most difficult conditions. The triangular profile prevents rolling on the work surface and promotes stable and continuous use.

### STRENGTH AND DURABILITY

The chrome-plated steel blade with sandblasted finish offers protection against corrosion and wear. The black phosphated tip ensures a precise fit with the screw and reduces the risk of slipping, prolonging the life of the tool.



### TRIMATERIAL STRUCTURE

The rigid polypropylene inner core is combined with soft, high-grip bits to ensure superior torque transmission.



### CONTROLLED DEFORMATION

The soft areas deform in a controlled manner, adapting to the point of contact and amplifying the thrust without fatiguing the hand.



### ANTI-ROTATION



The triangular shape prevents rolling on the workbench, improving safety and stability.

## Dimensions



## Certifications and Standards

## Coded items

	Art.		L mm	L1 mm	Ø mm	 g
012270105	1227TX 05	T5	50	151	3	37
012270106	1227TX 06	T6	50	151	3	37
012270107	1227TX 07	T7	50	151	3	37
012270108	1227TX 08	T8	60	161	3	39
012270109	1227TX 09	T9	60	169	4	60
012270110	1227TX 10	T10	80	189	4	62
012270115	1227TX 15	T15	80	189	4	62
012270120	1227TX 20	T20	100	209	4,5	68
012270125	1227TX 25	T25	100	209	5	72
012270127	1227TX 27	T27	115	236	6	106
012270130	1227TX 30	T30	115	236	6	106
012270140	1227TX 40	T40	130	263	7	140
012270145	1227TX 45	T45	130	263	8	159

**Scan the QR Code to access the web tab**

Specs, media and documentation in one click.

