

Antenna Cable SMA jack bulkhead to I-PEX Inc., MHF® I plug 1.37 20 cm thread length 10 mm

Description

The antenna cable by Delock is suitable for connecting components of radio frequency technology.



Item no. 88816

EAN: 4043619888160

Country of origin: Taiwan,
Republic of China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x SMA jack bulkhead >
 - 1 x I-PEX Inc., MHF® I plug
- Thread length: 10 mm
- Impedance: 50 Ohm
- Cable: coaxial
- Cable type: 1.37
- Cable attenuation: 2.5 dB @ 2.4 GHz per meter
- Cable diameter: ca. 1.37 mm
- Smallest bending radius: 9 mm
- Frequency: to 6 GHz
- Cable colour: grey
- Length incl. connectors (L): ca. 20 cm

System requirements

- Device with one free SMA or I-PEX Inc., MHF® I port

Package content

- Antenna cable
- Nut, toothed washer

Interface

Connector 1:	1 x SMA jack bulkhead
Connector 2:	1 x I-PEX Inc., MHF® I plug

Technical characteristics

Impedance:	50 Ω
------------	------

Physical characteristics

Thread length:	10 mm
Cable category:	coaxial
Cable type:	1.37
Cable attenuation:	2.5 dB @ 2.4 GHz per meter
Cable colour:	grey
Cable length incl. connectors:	20 cm
Smallest bending radius:	9 mm
Cable diameter:	1.37 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

