

USB 3.2 Gen 1 Hub with 4 Ports and Gigabit LAN and PD

Description

The USB hub by Delock is the mobile companion for laptops or tablets with USB Type-C™ connection. Up to three USB Type-A devices and one USB-C™ device can be connected to the hub.

Integrated 10/100/1000 Mbps LAN interface

In addition, the hub with **integrated RJ45 Gigabit LAN connection** expands a PC or laptop by a network interface via the USB Type-C™ connection.

USB Power Delivery (USB PD 3.0) support up to 100 watt

The hub has a **USB Type-C™ Power Delivery port** to connect the laptop or tablet to charge it.

Small sturdy helper

Due to its **small dimensions** and its **sturdy housing**, this Delock Hub is particularly suitable for travelling. It can simply be packed into the bag together with the laptop or tablet and used as needed.



Item no. 63252

EAN: 4043619632527

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x SuperSpeed USB (USB 3.2 Gen 1) USB Type-C™ male >
 - 2 x SuperSpeed USB (USB 3.2 Gen 1) Type-A female
 - 1 x SuperSpeed USB (USB 3.2 Gen 1) Type-A female - Battery Charging specification BC1.2
 - 1 x SuperSpeed USB (USB 3.2 Gen 1) USB Type-C™ Power Delivery female
 - 1 x Gigabit LAN RJ45 jack
- Chipset: VIA VL102, VL817, Realtek RTL8153
- Data transfer rate:
 - USB 3.2 Gen 1 up to 5 Gbps
 - Ethernet up to 10 Mbps (Half/Full Duplex)
 - Fast Ethernet up to 100 Mbps (Half/Full Duplex)
 - Gigabit Ethernet up to 1000 Mbps (Half/Full Duplex)
- Compatible with:
 - IEEE 802.3: 10BASE-T
 - IEEE 802.3u: 100BASE-TX
 - IEEE 802.3ab: 1000BASE-T

- Supports Auto MDI-X (automatic detection of standard or crossover network cable)
- Supports IEEE 802.3az (Energy Efficient Ethernet)
- Supports IEEE 802.1Q Virtual LAN (VLAN)
- Support full duplex operation with IEEE 802.3x flow control and half duplex operation with back-pressure flow control
- Supports 4k Jumbo Frames
- Cable length without connectors: ca. 15 cm
- Dimensions (LxWxH): ca. 95 x 45 x 13 mm
- Plug & Play

System requirements

- Android 9.1 or above
- Chrome OS 78.0 or above
- iPad Pro (2018)
- Linux Kernel 4.9 or above
- Mac OS 10.15.2 or above
- Windows 8.1/8.1-64/10/10-64
- Laptop or tablet with a free USB Type-C™ or Thunderbolt™ 3 port

Package content

- USB hub + LAN
- User manual

Images



General

Function:	Plug & Play
Supported operating system:	Android 9.1 or above Chrome OS 78.0 or above Linux Kernel 4.9 or above Mac OS 10.15.2 or above Windows 10 32-Bit Windows 10 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit iPad Pro (2018)

Interface

Connector 1:	1 x USB 5 Gbps USB Type-C™ male
Connector 2:	1 x Gigabit LAN RJ45 jack
Connector 3:	2 x USB 5 Gbps Type-A female
Connector 4:	1 x USB 5 Gbps Type-A female - Battery Charging specification BC1.2
Connector 5:	1 x USB 5 Gbps USB Type-C™ Power Delivery female

Technical characteristics

Data transfer rate:	Gigabit Ethernet up to 1 Gbps USB 3.2 Gen 1 up to 5 Gbps
---------------------	---

Physical characteristics

Cable length without connectors:	15 cm
----------------------------------	-------

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de