

3 Port USB 5 Gbps Hub + Gigabit LAN with USB Type-C™ or USB Type-A connector in metal case

Description

This solid USB hub by Delock with **metal housing** can be connected to a computer, laptop or mobile device via the **USB Type-A or USB-C™ interface**. Up to **3 USB devices** can be connected to the hub.

Integrated 10/100/1000 Mbps LAN interface

In addition, the hub with integrated **RJ45 Gigabit LAN connection** expands a PC or laptop by a network interface.

Extensive connectivity

Due to the specially designed adapter, the Delock hub can be quickly and easily connected to the USB Type-A socket. Thus, it can be easily connected to new devices with USB Type-C™ female and older devices that only have a USB Type-A connector. The **adapter is located directly on the cable** and therefore it cannot be lost.

Small, stable and handy

Due to its **small dimensions and its sturdy housing**, this Delock hub is particularly suitable for travelling. It can simply be packed into the bag together with the laptop or tablet and used as needed.



Item no. 64282

EAN: 4043619642823

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB 5 Gbps USB Type-C™ male
 - 3 x USB 5 Gbps Type-A female
 - 1 x Gigabit LAN RJ45 jack
- Adapter:
 - 1 x USB 5 Gbps USB Type-C™ female
 - 1 x USB 5 Gbps Type-A male
- Chipset: Genesys Logic GL3510, Realtek RTL8153
- Data transfer rate:
 - Ethernet up to 10 Mbps (Half/Full Duplex)
 - Fast Ethernet up to 100 Mbps (Half/Full Duplex)
 - Gigabit Ethernet up to 1000 Mbps (Half/Full Duplex)
- Compatible with:
 - IEEE 802.3: 10BASE-T
 - IEEE 802.3u: 100BASE-TX
 - IEEE 802.3ab: 1000BASE-T
- Supports Auto MDI-X (automatic detection of standard or crossover network cable)

- Supports Wake On LAN (WOL)
- Supports IEEE 802.3az (Energy Efficient Ethernet)
- Supports IEEE 802.1Q Virtual LAN (VLAN)
- Support full duplex operation with IEEE 802.3x flow control and half duplex operation with back-pressure
- Supports 4k Jumbo Frames
- Robust metal housing
- Dimensions (LxWxH): ca. 86 x 30 x 17 mm
- Cable length incl. connector: ca. 20 cm
- Colour: grey
- Plug & Play

System requirements

- Android 13.0 or above
- Chrome OS
- Linux Kernel 5.19 or above
- Mac OS 12.4 or above
- Windows 10/10-64/11
- iPad Air (4th Generation) or above
- iPad Pro (3rd Generation) or above
- Surface Pro 7
- Device with a free USB Type-C™ port or with a free Thunderbolt™ 3 or Thunderbolt™ 4 port or
- A free USB Type-A port

Package content

- USB hub + LAN
- User manual

Images



General

Function:	Plug & Play
Supported operating system:	Chrome OS Surface Pro 7 Windows 10 32-Bit Windows 10 64-Bit iPad Pro (3rd Generation) or above iPad Air (4th Generation) or above Windows 11 Mac OS 12.4 oder höher Android 13.0 or above Linux Kernel 5.19 or above

Interface

Connector 1:	1 x USB 5 Gbps USB Type-C™ male
Connector 2:	3 x USB 5 Gbps Type-A female
Connector 3:	1 x Gigabit LAN RJ45 jack

Technical characteristics

Chipset:	Realtek RTL8153 Genesys Logic GL3510
Data transfer rate:	5 Gbps

Physical characteristics

Cable length:	20 cm
Length:	86 mm
Width:	30 mm
Height:	17 mm
Colour:	grey

Manufacturer information

Street Beeskowdamm 13/15
 Postal code 14167

City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de