

SPG3-B-15C

## Surge protector, 5 sockets, 15 ft

### PURE POWER

- Protects valuable equipment from harmful power surges
- Suitable for high power consumption devices
- Overload protection



### Features

- GS approved surge protector with German type AC sockets
- Power surge and over-voltage suppression: protects computers, other office equipment and home appliances from harmful power surges and spikes
- 16 A automatic circuit breaker
- High quality, flame retardant plastic case
- Mounting holes
- VDE-approved power cord with German plug
- Power rocker switch with indicator light

### Packaging

Q'ty in crtn, pcs	20
Crtn volume, CUM	0.041
Crtn weight, kgs	17.6
Individual package size LxWxH:	105x45x340 mm
Carton size LxWxH:	440x345x270 mm
Country of origin	CN
Barcode	8716309064033
Customs code	8536301000

### Specifications

Rating: up to 250 V AC, 16 A, safety class IP20  
Maximum surge voltage 4,500 V, maximum spike current 4,500 A

Sockets: 5 pcs, German type  
Cable length: 4.5 m

### Certificates

