

# Thunderbolt™ 3 Mini Docking Station 8K - DisplayPort / HDMI / USB / LAN / Audio / PD 3.0

## Description

This Thunderbolt™ 3 **mini docking station** by Delock can be connected to a computer with a Thunderbolt™ 3 port and provides a variety of interfaces. The **DisplayPort output** allows the connection of an **8K display**, the **HDMI output** a connection of a **4K display**, **two monitors with 4K resolution** can be operated simultaneously. **Two built-in USB ports** allow the use of peripherals, connections for **headset and Gigabit network** complete the features.



**Item no. 87789**

EAN: 4043619877898

Country of origin: China

Package: Retail Box



Certified

### Multi-Stream Transport (MST)

The product is an MST hub and supports the extended desktop configuration of DisplayPort. This allows multiple monitors to be combined into one large display. Thereby the docking station supports a maximum resolution of up to **4K 60 Hz** per monitor.

### USB Power Delivery (USB PD 3.0) support up to 60 watt

The docking station has a USB Type-C™ Power Delivery port to connect the power supply of the laptop or tablet to charge it.

### Plug & Play

This device can simply be plugged in and is **immediately ready for use**. No extra power supply is needed when using the docking station.

### Small sturdy helper

Due to its **small dimensions and its sturdy housing**, this Delock docking station is particularly suitable for travelling. It can simply be packed into the bag together with the laptop or tablet and used as needed.

## Technical details

- Connectors:
  - 1 x Thunderbolt™ 3 male
  - 2 x USB 10 Gbps Type-A female
  - 1 x DisplayPort female
  - 1 x HDMI-A female
  - 1 x Gigabit LAN 10/100/1000 Mbps RJ45 jack
  - 1 x Headset 3.5 mm 4 pin jack
  - 1 x USB Type-C™ female (power supply)
- Chipset: Intel Titan Ridge
- Maximum resolution (depending on the system and the connected hardware):
  - DisplayPort up to 7680 x 4320 @ 30 Hz
  - HDMI up to 3840 x 2160 @ 60 Hz
  - DisplayPort + HDMI up to 3840 x 2160 @ 60 Hz
- Transmission of audio and video signals
- Functions: Mirrored or Extended
- Supports HDCP 2.2
- Supports HDR
- Headset jack: auto detection OMTP or CTIA standard
- Plug & Play
- Output power for host: max. 60 W
- 2 x LED indicator
- Colour: black
- Cable length without connectors: ca. 20 cm
- Dimensions (LxWxH): ca. 100 x 100 x 25 mm

---

## System requirements

- Mac OS 11.2.3 or above
- Windows 10/10-64/11
- PC or laptop with a free Thunderbolt™ 3 or Thunderbolt™ 4 port

---

## Package content

- Thunderbolt™ 3 docking station
- User manual

## Images



## General

Function:	Plug & Play HDR / HDR10
Supported operating system:	Windows 10 32-Bit Windows 10 64-Bit Mac OS 11.2.3 or above Windows 11
LED indicator:	2 x

## Interface

Connector 1:	1 x Thunderbolt™ 3 male
Connector 2:	1 x DisplayPort female 1 x HDMI female
Connector 3:	1 x Gigabit LAN RJ45 jack
Connector 4:	1 x Headset 3.5 mm 4 pin jack

## Technical characteristics

Maximum screen resolution:	7680 x 4320 @ 30 Hz
----------------------------	---------------------

## Physical characteristics

Housing material:	Plastic
Cable length:	20 cm
Length:	100 mm
Width:	100 mm
Height:	25 mm
Colour:	black

## Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland

E-Mail	<a href="mailto:info@delock.de">info@delock.de</a>
Website	<a href="http://www.delock.de">www.delock.de</a>