

Cable Seal M25x1,5 Metal 14-17mm



Part number	19 12 000 5058
Specification	Cable Seal M25x1,5 Metal 14-17mm
HARTING eCatalogue	https://b2b.harting.com/19120005058

Identification

Category	Accessories
Series of hoods/housings	Han-Compact®
Type of accessory	Cable gland
Description of the accessory	for hoods

Technical characteristics

Limiting temperature	-40 ... +130 °C
Tightening torque	≤10 Nm (depending on the cable and the seal insert used)
Wrench size	28
Degree of protection acc. to IEC 60529	IP65
Size	M25
Clamping range	14 ... 17 mm

Material properties

Material (cable glands)	Metal
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead



Pushing Performance

Commercial data

Packaging size	10
Net weight	23.32 g
Country of origin	Germany
European customs tariff number	84849000
eCl@ss	27144432 Screwed cable gland (electr.)